



GE Consumer & Industrial - Electrical Distribution

600V Max 50/60 Hz  
2 and 3 pole

- Curve Applies to:
- FG(N,H,L,P)2AA0250
  - FG(N,H,L,P)3AA0250
  - FG(N,H,L,P)2AA0400
  - FG(N,H,L,P)3AA0400
  - FG(N,H,L,P)2AA0600
  - FG(N,H,L,P)3AA0600

**Molded Case Circuit Breaker**

with SMR1 Solid State Trip  
Record Plus™ Type FG, 600A Frame

**DES-207**

Adjustable instantaneous 2-11, 2-13.5x Sensor  
In = Sensor Rating in Amps  
Inst = Breaker Dial Position  
Interruption ratings per DEA-382