



Load Center Replacement Fronts

United States

Single Phase

Main Ampere Rating	Load Center Cat. No.	Mod. No.	Front Cat. No.
60	TM860FCUGEN	M01	TMGPFC
	TM860SCUGEN	M01	TMGPSC
100	TM1210C24	M01	TLM12C24
	TM1210C24G	M01	TLM12C24
	TM1210CCU	M01	TM12FC
	TM1210CCU	M02	TLM12FD
	TM1210CCUG	M01	TM12FC
	TM1210CCUG	M02	TLM12FD
	TM2010CCU	M01	TM2010
	TM3210CCU	M01	TM3210
125	TLM1212C24	M01	TLM12C24
	TLM1212C24G	M01	TLM12C24
	TLM1212CCU	M01	TLM12BC
	TLM1212CCU	M02	TLM12BD
	TLM1212CCUG	M01	TLM12BC
	TLM1212CCUG	M02	TLM12BD
	TLM1612CCU	M01	TLM1612
	TLM2412CCU	M01	TLM2412
	TLM612FCU	M01	TLM6FC
	TLM612FCUD	M01	TLM6FCD
	TLM612SCU	M01	TLM6SC
	TLM612SCUD	M01	TLM6SCD
	TLM612SCUDG	M01	TLM6SCD
	TLM812FCU	M01	TLM8FC
	TLM812FCU	M01	TLM8SC
	TLM812FCUD	M01	TLM8FCD
	TLM812FCUDG	M01	TLM8FCD
	TLM812SCU	M01	TLM8SC
	TLM812SCUD	M01	TLM8SCD
	TLM812SCUDG	M01	TLM8SCD
	TM1212C24	M01	TLM12C24
	TM1212C24G	M01	TLM12C24
	TM1212CCU	M01	TM12FC
	TM1212CCU	M02	TLM12FD
	TM1212CCUG	M01	TM12FC
	TM1212CCUG	M02	TLM12FD
	TM1612CCU	M01	TLM1612
	TM1612CCUG	M01	TLM1612
	TM2412CCU	M01	TM24DC
150	TLM2015CCU	M01	TLM20BC
	TLM2015CCU	M06	TLM20BCD
	TLM2015CCU	M07	TLM2015
	TLM2415CCU	M01	TLM24DC
	TLM2415CCU	M06	TLM2415
	TM1615CCU	M01	TM16FC
	TM1615CCU	M06	TLM1620
	TM1615CCUG	M01	TM16FC
	TM1615CCUG	M06	TLM1620
	TM2015CCU	M01	TM20CX
	TM2015CCU	M06	TM20CXD
	TM2015CCU	M07	TLM2015
	TM2415CCU	M01	TM24EC
	TM2415CCU	M06	TLM2415
	TM2415CCUB	M01	TMB24BD
	TM3215C42	M06	TLM32C42
	TM3215CCU	M01	TM32C
	TM3215CCU	M06	TLM3215
200	TLM1620CCU	M01	TLM16BC
	TLM1620CCU	M06	TLM16BCD
	TLM1620CCU	M07	TLM1620
	TLM1620CCUG	M01	TLM16BC
	TLM1620CCUG	M06	TLM16BCD
	TLM1620CCUG	M07	TLM1620
	TLM2020CCU	M01	TLM20DC
	TLM2020CCU	M06	TLM20DCD
	TLM2020CCU	M07	TLM2020
	TLM2020CCUG	M01	TLM20DC
	TLM2020CCUG	M06	TLM20DCD
	TLM2020CCUG	M07	TLM2020

Main Ampere Rating	Load Center Cat. No.	Mod. No.	Front Cat. No.
200 (continued)	TLM3220C42	M07	TLM32C42
	TLM3220CCU	M01	TLM32AC
	TLM3220CCU	M06	TLM32ACD
	TLM3220CCU	M07	TLM32C42
	TLM3220CCUW	M06	TLM32ACWD
	TLM4020CCU	M01	TLM40AC
	TLM4020CCU	M06	TLM4020
	TLM4220CCU	M06	TLM4222
	TM1620CCU	M01	TM16GC
	TM1620CCU	M06	TM16GCD
	TM1620CCU	M07	TLM1620
	TM1620CCUG	M01	TM16GC
	TM1620CCUG	M06	TM16GCD
	TM1620CCUG	M07	TLM1620
	TM2020CCU	M01	TM20EC
	TM2020CCU	M06	TM20ECD
	TM2020CCU	M07	TLM2020
	TM2020CCUB	M01	TMB20BC
	TM2020CCUG	M01	TM20EC
	TM2020CCUG	M06	TM20ECD
	TM2020CCUG	M07	TLM2020
	TM2020CCUW	M07	TM20FDWD
	TM3220C42	M06	TM32GCD
	TM3220C42	M07	TLM3220
	TM3220CCU	M01	TM32FC
	TM3220CCU	M06	TM32FCD
	TM3220CCU	M07	TLM3220
	TM3220CCUB	M01	TMB32C
	TM4020CCU	M01	TM40BC
	TM4020CCU	M06	TLM4020
	TM4020CCU	M07	TMB40AC
	TM4220CCU	M06	TLM4222
225	TLM4222CCU	M01	TLM42CM
	TLM4222CCU	M06	TLM4222
	TLM2020CCUW	M06	TLM20ACWD
	TLM2020CCUW	M07	TLM20W

Three Phase

Main Ampere Rating	Load Center Cat. No.	Mod. No.	Front Cat. No.
100	TM12410C	M02	TM12AC3
	TM18410C	M02	TM18AC3
125	TL12412C	M02	TL12AC3
	TM30412C	M03	TM30EC3
	TM30412CB	M03	TMB30BC3
150	TL18415C	M02	TL18BC3
	TL24415C	M02	TL24AC3
	TM24415C	M03	TM24DC3
	TM24415CB	M03	TMB24BC3
	TM30415C	M03	TM30EC3
	TM30415CB	M03	TMB30EC3
	TM42415C	M03	TM42DC3
	TM42415CB	M03	TMB42DC3
200	TL18420C	M02	TL18DC3
	TL30420C	M02	TL30BC3
	TL42420C	M02	TL42BC3
	TM24420C	M02	TM24DC3
	TM24420CB	M02	TMB24DC3
	TM30420C	M03	TM30DC3
	TM30420CB	M03	TMB30DC3
	TM42420C	M03	TM42EC3
	TM42420CB	M03	TMB42EC3
225	TL30422C	M01	TL30AC3
	TL42422C	M01	TL42AC3
	TM42422C	M02	TM42BC3
	TM42422CB	M02	TMB42BC3

Most of the items in the shaded rows are obsolete. In addition to ordering the replacement front with the largest model number, order a new THQM (KR main). The catalog number will be THQMXXXX where XXX is the main breaker amp rating. Example: THQM200D for a 200A main breaker.

Load Center Replacement Fronts

Canada

Single Phase

Main Ampere Rating	Load Center Cat. No.	Mod. No.	Front Cat. No.
100	TMC1210CCA	M01	TMC12A
	TMC1210CCU	M01	TMC12A
	TMC1610CCA	M01	TMC16A
	TMC1610CCU	M01	TMC16A
	TMC2010CCA	M01	TMC20A
	TMC2010CCU	M01	TMC20A
	TMC2410CCA	M01	TMC24A
	TMC2410CCU	M01	TMC24A
	TMC3210CCA	M01	TMC32A
	TMC3210CCU	M01	TMC32A
125	TLC1212CCA	M01	TLC12A
	TLC1212CCU	M01	TLC12A
	TLC1612CCA	M01	TLC16A
	TLC1612CCU	M01	TLC16A
	TLC2412CCA	M01	TLC24A
	TLC2412CCU	M01	TLC24A
	TLC612FCU	M01	TLC6FC
	TLC612FCUD	M01	TLC8FCFD
	TLC612SCU	M01	TLC6SC
	TLC612SCUD	M01	TLC6SCD
	TLC812FCU	M01	TLC8FC
	TLC812FCUD	M01	TLC8FCFD
	TLC812SCU	M01	TLC8SCD
	TLC812SCUD	M01	TLC8SCD
	TMC1612CCA	M01	TMC16B
	TMC1612CCU	M01	TMC16B
	TMC2012CCA	M01	TMC20B
	TMC2012CCU	M01	TMC20B
	TMC2412CCA	M01	TMC24B
	TMC2412CCU	M01	TMC24B
	TMC3212CCA	M01	TMC32B
	TMC3212CCU	M01	TMC32B
150	TMC2015CCA	M06	TMC20CD
	TMC2015CCU	M01	TMC20C
	TMC2015CCU	M06	TMC20CD
	TMC2415CCA	M06	TMC24CD
	TMC2415CCU	M01	TMC24C
	TMC2415CCU	M06	TMC24CD
	TMC3215CCA	M06	TMC32CD
	TMC3215CCU	M01	TMC32C
	TMC3215CCU	M06	TMC32CD
	TMC4015CCA	M06	TMC40AD
	TMC4015CCU	M01	TMC40A
	TMC4015CCU	M06	TMC40AD
200	TLC1620CCA	M01	TLC16B
	TLC1620CCU	M01	TLC16B
	TLC2020CCA	M01	TLC20A
	TLC2020CCU	M01	TLC20A
	TLC3220CCA	M01	TLC32A
	TLC3220CCU	M01	TLC32A
	TLC4020CCA	M01	TLC40A
	TLC4020CCU	M01	TLC40A
	TMC2020CCA	M06	TMC20DD
	TMC2020CCU	M01	TMC20D
	TMC2020CCU	M06	TMC20DD
	TMC3220CCA	M06	TMC32DD
	TMC3220CCU	M01	TMC32D
	TMC3220CCU	M06	TMC32DD
	TMC4020CCA	M06	TMC40BD
	TMC4020CCU	M01	TMC40B
	TMC4020CCU	M06	TMC40BD
225	TLC4222CCA	M01	TLC42A
	TLC4222CCU	M01	TLC42A

Three Phase

Main Ampere Rating	Load Center Cat. No.	Mod. No.	Front Cat. No.
100	TMC12410C	M01	TMC124A
	TMC18410C	M01	TMC184A
125	TMC30412C	M01	TMC304A
	TLC18415C	M01	TLC184A
150	TLC24415C	M01	TLC244A
	TLC18420C	M01	TLC184B
200	TLC30420C	M01	TLC304A
	TLC42420C	M01	TLC424A
	TMC42420C	M03	TMC424A
225	TLC30422C	M01	TLC304B
	TLC42422C	M01	TLC424B

International

Single Phase

Main Ampere Rating	Load Center Cat. No.	Mod. No.	Front Cat. No.
125	TLM1212CCUX2	M01	TLM12ACX
	TLM1612CCUX2	M01	TLM16ACX
	TLM2412CCUX2	M01	TLM2412
	TLM612FCUDX2	M01	TLM6FCD
	TLM612SCUDX2	M01	TLM6SCD
	TLM812FCUDX2	M01	TLM8FCD
	TLM812SCUDX2	M01	TLM8SCD
150	TL1615CCUX2	M01	TL16CX
	TL2015CCUX2	M01	TL20CX
200	TL2020CCUX2	M01	TL20ACX
	TL3220CCUX2	M01	TL32CX
225	TL4020CCUX2	M01	TL40CX
	TL4222CCUX2	M01	TL42DCX

Three Phase

Main Ampere Rating	Load Center Cat. No.	Mod. No.	Front Cat. No.
100	TM12410CBX2	M01	TM12CBX2
	TM12410CBX2	M01	TM12CBX2
	TM12410CX2	M02	TM12ACX
	TM12410CX2LB	M02	TM12ACX
	TM18410CX2	M02	TM18ACX
125	TL12412CX2	M02	TL12ACX
	TM30412CX2	M02	TM30BCX
150	TL18415CX2	M02	TL18ACX
	TL24415CX2	M02	TL24ACX
	TM24415CBX2	M02	TMB24BCX
	TM24415CBX2LB	M02	TMB24BCX
	TM24415CX2	M02	TM24BCX
	TM24415CX2LB	M02	TM24BCX
	TM30415CX2	M02	TM30BCX
	TM30415CX2LB	M02	TM30BCX
	TM42415CX2	M02	TM42DCX
	TL18420CX2	M02	TL18BCX
200	TL30420CX2	M02	TL30DCX
	TL42420CX2	M02	TL42BCX
	TM24420CX2	M02	TM24DCX
	TM24420CX2	M02	TM24DCX
	TM30420CX2	M02	TM30DCX
	TM42420CX2	M02	TM42ECX
	TM42420CX2	M02	TM42ECX
	TM42420CX2LB	M02	TM42ECX
	TL30422CX2	M01	TL30ACX
	TL42422CX2	M01	TL42ACX
225	TM42422CX2	M01	TM42BCX
	TM42422CX2	M01	TM42BCX

Most of the items in the shaded rows are obsolete. In addition to ordering the replacement front with the largest model number, order a new THQMV (KR main).

The catalog number will be THQMVXXXD where XXX is the main breaker amp rating. Example: THQMV200D for a 200A main breaker.