



GE Energy Connections

# Spectra Switchboard and Power Panel Circuit Breaker and Mounting Kit Selection Guide

GE  
4200 Wildwood Parkway  
Atlanta, GA. 30339 USA

## Using the Ampere, Frame, and kAIC Rating, Select the Appropriate Circuit Breaker

- For Spectra RMS, Include (1) rating plug per circuit breaker; For all other breaker types, no rating plug is required.
- If Lugs are included in the listed circuit breaker catalog number, "Included" will be listed in the *Terminal Lug* column. If lugs are required to be purchased separately, the most common (typical) lug catalog number will be listed. 3-Pole circuit breakers require (3) lugs; 2-Pole circuit breakers require (2) lugs

## Using the Required Mounting Configuration, Select the Appropriate Bolt-on Mounting Kit

- The Mounting Kit Poles must be equal to or greater than the circuit breaker poles
  - 1- Pole CB = 2 or 3 Pole Mounting Kit
  - 2- Pole CB = 2 or 3 Pole Mounting Kit
  - 3-Pole CB = 3 Pole Mounting Kit
- Mounting Kits and filler plates should be ordered separately
- Fillers for unused spaces may also be ordered separately (p. 16)

Ampere Rating & Rating Plug Catalog #

CB Catalog Numbers by kAIC

Lug Catalog #  
(If not included  
in CB cat #)

Mounting Kit by # of Poles & Single or Dual Mounting

### Spectra G-Frame, 2-Pole

UL 489 IC rating @ 480V

Terminal Lug

Spectra Bolt-On Mounting Kit

AMPERE RATING	RATING PLUG	FRAME AMPS	65KA / 240V ONLY	35KA	65KA	100KA	TYPICAL	3-POLE	2-POLE
125	SRPG400A125	400	SGDA22AT0400	SGHA26AT0400	SGLA26AT0400	SGPA26AT0400	TCLK265 (Order 1 kit)	<b>Dual Mounted</b> Mounting Kit - AMBC6GB Filler Plate - AFP4SGD	<b>Dual Mounted</b> Mounting Kit - AMCB4GB Filler Plate - AFP4GSGD
150	SRPG400A150								
175	SRPG400A175								
200	SRPG400A200								
225	SRPG400A225								
250	SRPG400A250								
300	SRPG400A300								
350	SRPG400A350								
400	SRPG400A400								
250	SRPG600A250	600		SGHA26AT0600	SGLA26AT0600	SGPA26AT0600	TCLK265 (Order 1 kit)	<b>Single Mounted</b> Mounting Kit - AMCB3GM Filler Plate - AFP4SGS	<b>Single Mounted</b> Mounting Kit - AMCB2GM Filler Plate - AFP4SGS
300	SRPG600A300								
350	SRPG600A350								
400	SRPG600A400								
450	SRPG600A450								
500	SRPG600A500								
600	SRPG600A600								

# Spectra RMS

## Spectra E-Frame, 2-Pole

UL 489 IC rating @ 480V

Terminal Lug

Spectra Bolt-On Mounting Kit

AMPERE RATING	RATING PLUG	FRAME AMPS	18KA	25KA	65KA	100KA	TYPICAL	3-POLE	2-POLE	
15	SRPE30A15	30	SEDA24AT0030	SEHA24AT0030	SELA24AT0030	SEPA24AT0030	TCAL18 (Order 2)	<b>Dual Mounted</b> Mounting Kit - AMCB6EB Filler Plate - AFP3SED	<b>Dual Mounted</b> Mounting Kit - AMCB4SE Filler Plate - AFP3SED	
20	SRPE30A20									
25	SRPE30A25									
30	SRPE30A30									
35	SRPE60A35	60	SEDA24AT0060	SEHA24AT0060	SELA24AT0060	SEPA24AT0060		<b>Single Mounted</b> N/A - N/A	<b>Single Mounted</b> N/A - N/A	
40	SRPE60A40									
45	SRPE60A45									
50	SRPE60A50									
60	SRPE60A60									
70	SRPE100A70	100	SEDA24AT0100	SEHA24AT0100	SELA24AT0100	SEPA24AT0100				
80	SRPE100A80									
90	SRPE100A90									
100	SRPE100A100									
110	SRPE150A110	150	SEDA24AT0150	SEHA24AT0150	SELA24AT0150	SEPA24AT0150				
125	SRPE150A125									
150	SRPE150A150									

## Spectra E-Frame, 3-Pole

UL 489 IC rating @ 480V

Terminal Lug

Spectra Bolt-On Mounting Kit

AMPERE RATING	RATING PLUG	FRAME AMPS	18KA	25KA	65KA	100KA	TYPICAL	3-POLE	2-POLE		
15	SRPE30A15	30	SEDA36AT0030	SEHA36AT0030	SELA36AT0030	SEPA36AT0030	TCAL18 (Order 3)	<b>Dual Mounted</b> Mounting Kit - AMCB6EB Filler Plate - AFP3SED	N/A		
20	SRPE30A20										
25	SRPE30A25										
30	SRPE30A30										
35	SRPE60A35	60	SEDA36AT0060	SEHA36AT0060	SELA36AT0060	SEPA36AT0060		<b>Single Mounted</b> N/A - N/A			
40	SRPE60A40										
45	SRPE60A45										
50	SRPE60A50										
60	SRPE60A60										
70	SRPE100A70	100	SEDA36AT0100	SEHA36AT0100	SELA36AT0100	SEPA36AT0100					
80	SRPE100A80										
90	SRPE100A90										
100	SRPE100A100										
110	SRPE150A110	150	SEDA36AT0150	SEHA36AT0150	SELA36AT0150	SEPA36AT0150					
125	SRPE150A125										
150	SRPE150A150										

## Spectra RMS (Cont.)

### Spectra F-Frame, 2-Pole

UL 489 IC rating @ 480V

Terminal Lug

Spectra Bolt-On Mounting Kit

AMPERE RATING	RATING PLUG	FRAME AMPS	35KA	65KA	100KA	TYPICAL	3-POLE	2-POLE
70	SRPF250A70	250	SFHA24AT0250	SFLA24AT0250	SFPA24AT0250	TCAL29 (Order 2)	<b>Dual Mounted</b> Mounting Kit - AMCB6FJ Filler Plate - AFP3SFD	<b>Dual Mounted</b> Mounting Kit - AMCB4FJ Filler Plate - AFP3SFD
80	SRPF250A80							
90	SRPF250A90							
100	SRPF250A100							
110	SRPF250A110							
125	SRPF250A125							
150	SRPF250A150							
175	SRPF250A175							
200	SRPF250A200							
225	SRPF250A225							
250	SRPF250A250						<b>Single Mounted</b> Mounting Kit - AMCB3FJ Filler Plate - AFP3SFS	<b>Single Mounted</b> Mounting Kit - AMCB2FJ Filler Plate - AFP3SFS

### Spectra F-Frame, 3-Pole

UL 489 IC rating @ 480V

Terminal Lug

Spectra Bolt-On Mounting Kit

AMPERE RATING	RATING PLUG	FRAME AMPS	35KA	65KA	100KA	TYPICAL	3-POLE	2-POLE
70	SRPF250A70	250	SFHA36AT0250	SFLA36AT0250	SFPA36AT0250	TCAL 29 (Order 3)	<b>Dual Mounted</b> Mounting Kit - AMCB6FJ Filler Plate - AFP3SFD	N/A
80	SRPF250A80							
90	SRPF250A90							
100	SRPF250A100							
110	SRPF250A110							
125	SRPF250A125							
150	SRPF250A150							
175	SRPF250A175							
200	SRPF250A200							
225	SRPF250A225							
250	SRPF250A250						<b>Single Mounted</b> Mounting Kit - AMCB3FJ Filler Plate - AFP3SFS	

## Spectra RMS (Cont.)

### Spectra G-Frame, 2-Pole

UL 489 IC rating @ 480V

Terminal Lug

Spectra Bolt-On Mounting Kit

AMPERE RATING	RATING PLUG	FRAME AMPS	65KA / 240V ONLY	35KA	65KA	100KA	TYPICAL	3-POLE	2-POLE
125	SRPG400A125	400	SGDA22AT0400	SGHA26AT0400	SGLA26AT0400	SGPA26AT0400	TCLK265 (Order 1 lug kit)	<b>Dual Mounted</b> Mounting Kit - AMCB6GB Filler Plate - AFP4SGD	<b>Dual Mounted</b> Mounting Kit - AMCB4GB Filler Plate - AFP4SGD
150	SRPG400A150								
175	SRPG400A175								
200	SRPG400A200								
225	SRPG400A225								
250	SRPG400A250								
300	SRPG400A300								
350	SRPG400A350								
400	SRPG400A400	600		SGHA26AT0600	SGLA26AT0600	SGPA26AT0600	<b>Single Mounted</b> Mounting Kit - AMCB3GM Filler Plate - AFP4SGS	<b>Single Mounted</b> Mounting Kit - AMCB2GM AFP4SGS	
250	SRPG600A250								
300	SRPG600A300								
350	SRPG600A350								
400	SRPG600A400								
450	SRPG600A450								
500	SRPG600A500								
600	SRPG600A600								

### Spectra G-Frame, 3-Pole

UL 489 IC rating @ 480V

Terminal Lug

Spectra Bolt-On Mounting Kit

AMPERE RATING	RATING PLUG	FRAME AMPS	65KA / 240V ONLY	35KA	65KA	100KA	TYPICAL	3-POLE	2-POLE
125	SRPG400A125	400	SGDA32AT0400	SGHA36AT0400	SGLA36AT0400	SGPA36AT0400	TCLK365 (Order 1 lug kit)	<b>Dual Mounted</b> Filler Plate - AMCB6GB AFP4SGD	N/A
150	SRPG400A150								
175	SRPG400A175								
200	SRPG400A200								
225	SRPG400A225								
250	SRPG400A250								
300	SRPG400A300								
350	SRPG400A350								
400	SRPG400A400	600		SGHA36AT0600	SGLA36AT0600	SGPA36AT0600	<b>Single Mounted</b> Mounting Kit - AMCB3GM Filler Plate - AFP4SGS		
250	SRPG600A250								
300	SRPG600A300								
350	SRPG600A350								
400	SRPG600A400								
450	SRPG600A450								
500	SRPG600A500								
600	SRPG600A600								

## Spectra RMS (Cont.)

### Spectra K-Frame, 2-Pole

UL 489 IC rating @ 480V

Terminal Lug

Spectra Bolt-On Mounting Kit

AMPERE RATING	RATING PLUG	FRAME AMPS	50KA	65KA	100KA	TYPICAL	3-POLE	2-POLE
300	SRPK800A300	800	SKHA26AT0800	SKLA26AT0800	SKPA26AT0800	TCAL81 (Order 2)	<b>Single Mounted</b> Mounting Kit - AMCB3KM Filler Plate - AFP6SKS	<b>Single Mounted</b> Mounting Kit - AMCB2KM Filler Plate - AFP6SKS
400	SRPK800A400							
500	SRPK800A500							
600	SRPK800A600							
700	SRPK800A700							
800	SRPK800A800							
600	SRPK1200A600	1200	SKHA26AT1200	SKLA26AT1200	SKPA26AT1200	TCAL125 (Order 2)		
700	SRPK1200A700							
800	SRPK1200A800							
900	SRPK1200A900							
1000	SRPK1200A1000							
1175	SRPK1200A1175							
1200	SRPK1200A1200							

### Spectra K-Frame, 3-Pole

UL 489 IC rating @ 480V

Terminal Lug

Spectra Bolt-On Mounting Kit

AMPERE RATING	RATING PLUG	FRAME AMPS	50KA	65KA	100KA	TYPICAL	3-POLE	2-POLE
300	SRPK800A300	800	SKHA36AT0800 SKHH36AT0800*	SKLA36AT0800 SKLL36AT0800*	SKPA36AT0800 SKPP36AT0800*	TCAL81 (Order 3)	<b>Single Mounted</b> Mounting Kit - AMCB3KM Filler Plate - AFP6SKS	N/A
400	SRPK800A400							
500	SRPK800A500							
600	SRPK800A600							
700	SRPK800A700							
800	SRPK800A800							
600	SRPK1200A600	1200	SKHA36AT1200 SKHH36AT1200*	SKLA36AT1200 SKLL36AT1200*	SKPA36AT1200 SKPP36AT1200*	TCAL125 (Order 3)		
700	SRPK1200A700							
800	SRPK1200A800							
900	SRPK1200A900							
1000	SRPK1200A1000							
1175	SRPK1200A1175							
1200	SRPK1200A1200							

\*-100% RATED SK, USE LUG CAT #TCO124 OR TCO125

# TEB/TED/THED

## TEB/TED/THED, 1-Pole

AMPERE RATING						Terminal Lug	Spectra Bolt-On Mounting Kit	
	TEB 120V	TED 277V	TED 347V	THED277V	THED347V	TYPICAL	3-POLE	2-POLE
10	TEB111010	TED113010	—	—	—	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6EB Filler Plate - AFP3SED  <b>Single Mounted</b> N/A - N/A	<b>Dual Mounted</b> TEB, TED Mounting Kit - AMCB4EB TEB, TED Filler Plate - AFP2TED  THED Mounting Kit - AMCB4SE THED Filler Plate - AFP3SED  <b>Single Mounted</b> N/A - N/A
15	TEB111015	TED113015	TED114015	THED113015	THED114015			
20	TEB111020	TED113020	TED114020	THED113020	THED114020			
25	TEB111025	TED113025	TED114025	THED113025	THED114025			
30	TEB111030	TED113030	TED114030	THED113030	THED114030			
35	TEB111035	TED113035	—	—	—			
40	TEB111040	TED113040	—	—	—			
45	TEB111045	TED113045	—	—	—			
50	TEB111050	TED113050	—	—	—			
60	TEB111060	TED113060	—	—	—			
70	TEB111070	TED113070	—	—	—			
80	TEB111080	TED113080	—	—	—			
90	TEB111090	TED113090	—	—	—			
100	TEB111100	TED113100	—	—	—			

## TEB/TED/THED, 2-Pole

AMPERE RATING						Terminal Lug	Spectra Bolt-On Mounting Kit	
	TEB 240V	TED 480V	THED 480V			TYPICAL	3-POLE	2-POLE
10	TEB122010	TED124010	—	—	—	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6EB Filler Plate - AFP3SED  <b>Single Mounted</b> N/A - N/A	<b>Dual Mounted</b> TEB, TED Mounting Kit - AMCB4EB TEB, TED Filler Plate - AFP2TED  THED Mounting Kit - AMCB4SE THED Filler Plate - AFP3SED  <b>Single Mounted</b> N/A - N/A
15	TEB122015	TED124015	THED124015	—	—			
20	TEB122020	TED124020	THED124020	—	—			
25	TEB122025	TED124025	THED124025	—	—			
30	TEB122030	TED124030	THED124030	—	—			
35	TEB122035	TED124035	THED124035	—	—			
40	TEB122040	TED124040	THED124040	—	—			
45	TEB122045	TED124045	THED124045	—	—			
50	TEB122050	TED124050	THED124050	—	—			
60	TEB122060	TED124060	THED124060	—	—			
70	TEB122070	TED124070	THED124070	—	—			
80	TEB122080	TED124080	THED124080	—	—			
90	TEB122090	TED124090	THED124090	—	—			
100	TEB122100	TED124100	THED124100	—	—			
110	—	TED124110	—	—	—			
125	—	TED124125	—	—	—			
150	—	TED124150	—	—	—			

## TEB/TED/THED (Cont.)

### TEB/TED/THED, 3-Pole

Terminal Lug

Spectra Bolt-On Mounting Kit

AMPERE RATING	TEB 240 V	TED 480V	TED 600V	THED 600V		TYPICAL	3-POLE	2-POLE
10	TEB132010	TED134010	—	—	—	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6EB Filler Plate - AFP3SED  <b>Single Mounted</b> N/A - N/A	N/A
15	TEB132015	TED134015	—	—	—			
20	TEB132020	TED134020	TED136020	THED136020	—			
25	TEB132025	TED134025	TED136025	THED136025	—			
30	TEB132030	TED134030	TED136030	THED136030	—			
35	TEB132035	TED134035	TED136035	THED136035	—			
40	TEB132040	TED134040	TED136040	THED136040	—			
45	TEB132045	TED134045	TED136045	THED136045	—			
50	TEB132050	TED134050	TED136050	THED136050	—			
60	TEB132060	TED134060	TED136060	—	—			
70	TEB132070	TED134070	TED136070	THED136070	—			
80	TEB132080	TED134080	TED136080	—	—			
90	TEB132090	TED134090	TED136090	THED136090	—			
100	TEB132100	TED134100	TED136100	THED136100	—			
110	—	TED134110	TED136110	THED136110	—			
125	—	TED134125	TED136125	THED136125	—			
150	—	TED134150	TED136150	THED136150	—			



# TEY

## TEY/TEYF, F1-Pole

AMPERE RATING	UL489 IC Rating		Terminal Lug	Spectra Bolt-On Mounting Kit	
	14KA @ 480/277VAC	18KA @ 480/277VAC		3-POLE	2-POLE
15	TEY115	TEYF115	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6EY Filler Plate - AFP3EYD  <b>Single Mounted</b> N/A	<b>Dual Mounted</b> Mounting Kit - AMCB4EY Filler Plate - AFP3EYD  <b>Single Mounted</b> N/A
20	TEY120	TEYF120			
25	TEY125	TEYF125			
30	TEY130	TEYF130			
35	TEY135	TEYF135			
40	TEY140	TEYF140			
45	TEY145	TEYF145			
50	TEY150	TEYF150			
60	TEY160	TEYF160			
70	TEY170	TEYF170			
80	TEY180	TEYF180			
90	TEY190	TEYF190			
100	TEY1100	TEYF1100			

## TEY/TEYF, 2-Pole

AMPERE RATING	UL489 IC Rating		Terminal Lug	Spectra Bolt-On Mounting Kit	
	14KA @ 480/277VAC	18KA @ 480/277VAC		3-POLE	2-POLE
15	TEY215	TEYF215	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6EY Filler Plate - AFP3EYD  <b>Single Mounted</b> N/A	<b>Dual Mounted</b> Mounting Kit - AMBB4EY Filler Plate - AFP3EYD  <b>Single Mounted</b> N/A
20	TEY220	TEYF220			
25	TEY225	TEYF225			
30	TEY230	TEYF230			
35	TEY235	TEYF235			
40	TEY240	TEYF240			
45	TEY245	TEYF245			
50	TEY250	TEYF250			
60	TEY260	TEYF260			
70	TEY270	TEYF270			
80	TEY280	TEYF280			
90	TEY290	TEYF290			
100	TEY2100	TEYF2100			
110	—	TEYF2110B			
125	—	TEYF2125B			

## TEY (Cont.)

### TEY/TEYF, 3-Pole

AMPERE RATING	UL489 IC Rating		Terminal Lug	Spectra Bolt-On Mounting Kit	
	14KA @ 480/277VAC	18KA @ 480/277VAC		3-POLE	2-POLE
15	TEY315	TEYF315	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6EY Filler Plate - AFP3EYD  <b>Single Mounted</b> N/A - N/A	N/A
20	TEY320	TEYF320			
25	TEY325	TEYF325			
30	TEY330	TEYF330			
35	TEY335	TEYF335			
40	TEY340	TEYF340			
45	TEY345	TEYF345			
50	TEY350	TEYF350			
60	TEY360	TEYF360			
70	TEY370	TEYF370			
80	TEY380	TEYF380			
90	TEY390	TEYF390			
100	TEY3100	TEYF3100			
110	—	TEYF3110B			
125	—	TEYF3125B			

## TQD/THQD

### TQD/THQD, 2-Pole

AMPERE RATING	UL489 IC Rating		Terminal Lug	Spectra Bolt-On Mounting Kit	
	10KA @240VAC	22KA @240VAC	TYPICAL	3-POLE	2-POLE
100	TQD22100	THQD22100	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6QD Filler Plate - AFP3QDD	<b>Dual Mounted</b> Mounting Kit - AMCB4QD Filler Plate - AFP2QDD
125	TQD22125	THQD22125			
150	TQD22150	THQD22150			
175	TQD22175	THQD22175			
200	TQD22200	THQD22200			
225	TQD22225	THQD22225			

### TQD/THQD, 3-Pole

AMPERE RATING	UL489 IC Rating		Terminal Lug	Spectra Bolt-On Mounting Kit	
	10KA @240VAC	22KA @240VAC	TYPICAL	3-POLE	2-POLE
100	TQD32100	THQD32100	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6QD Filler Plate - AFP3QDD	N/A
125	TQD32125	THQD32125			
150	TQD32150	THQD32150			
175	TQD32175	THQD32175			
200	TQD32200	THQD32200			
225	TQD32225	THQD32225			

# Record Plus

## FB, 1-Pole

AMPERE RATING	UL489 IC Rating @ 480V				TYPICAL	Spectra Bolt-On Mounting Kit	
	35KA	65KA	100KA	150KA		3-POLE	2-POLE
15	FBV16TE015R2	FBN16TE015R2	FBH16TE015R2	FBL16TE015R2	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6FB Filler Plate - AFP3FBD	<b>Dual Mounted</b> Mounting Kit - AMCB4FB Filler Plate - AFP2FBD
20	FBV16TE020R2	FBN16TE020R2	FBH16TE020R2	FBL16TE020R2			
25	FBV16TE025R2	FBN16TE025R2	FBH16TE025R2	FBL16TE025R2			
30	FBV16TE030R2	FBN16TE030R2	FBH16TE030R2	FBL16TE030R2			
35	FBV16TE035R2	FBN16TE035R2	FBH16TE035R2	FBL16TE035R2			
40	FBV16TE040R2	FBN16TE040R2	FBH16TE040R2	FBL16TE040R2			
45	FBV16TE045R2	FBN16TE045R2	FBH16TE045R2	FBL16TE045R2			
50	FBV16TE050R2	FBN16TE050R2	FBH16TE050R2	FBL16TE050R2			
60	FBV16TE060R2	FBN16TE060R2	FBH16TE060R2	FBL16TE060R2			
70	FBV16TE070R2	FBN16TE070R2	FBH16TE070R2	FBL16TE070R2			
80	FBV16TE080R2	FBN16TE080R2	FBH16TE080R2	FBL16TE080R2			
90	FBV16TE090R2	FBN16TE090R2	FBH16TE090R2	FBL16TE090R2			
100	FBV16TE100R2	FBN16TE100R2	FBH16TE100R2	FBL16TE100R2			

## FB, 2-Pole

AMPERE RATING	UL489 IC Rating @ 480V				TYPICAL	Spectra Bolt-On Mounting Kit	
	35KA	65KA	100KA	150KA		3-POLE	2-POLE
15	FBV26TE015R2	FBN26TE015R2	FBH26TE015R2	FBL26TE015R2	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6FB Filler Plate - AFP3FBD	<b>Dual Mounted</b> Mounting Kit - AMCB4FB Filler Plate - AFP2FBD
20	FBV26TE020R2	FBN26TE020R2	FBH26TE020R2	FBL26TE020R2			
25	FBV26TE025R2	FBN26TE025R2	FBH26TE025R2	FBL26TE025R2			
30	FBV26TE030R2	FBN26TE030R2	FBH26TE030R2	FBL26TE030R2			
35	FBV26TE035R2	FBN26TE035R2	FBH26TE035R2	FBL26TE035R2			
40	FBV26TE040R2	FBN26TE040R2	FBH26TE040R2	FBL26TE040R2			
45	FBV26TE045R2	FBN26TE045R2	FBH26TE045R2	FBL26TE045R2			
50	FBV26TE050R2	FBN26TE050R2	FBH26TE050R2	FBL26TE050R2			
60	FBV26TE060R2	FBN26TE060R2	FBH26TE060R2	FBL26TE060R2			
70	FBV26TE070R2	FBN26TE070R2	FBH26TE070R2	FBL26TE070R2			
80	FBV26TE080R2	FBN26TE080R2	FBH26TE080R2	FBL26TE080R2			
90	FBV26TE090R2	FBN26TE090R2	FBH26TE090R2	FBL26TE090R2			
100	FBV26TE100R2	FBN26TE100R2	FBH26TE100R2	FBL26TE100R2			

## Record Plus (Cont.)

### FB, 3-Pole

AMPERE RATING	UL489 IC Rating @ 480V					TYPICAL	Spectra Bolt-On Mounting Kit	
	35KA	65KA	100KA	150KA	Terminal Lug		3-POLE	2-POLE
15	FBV36TE015R2	FBN36TE015R2	FBH36TE015R2	FBL36TE015R2	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6FB Filler Plate - AFP3FBD	N/A	
20	FBV36TE020R2	FBN36TE020R2	FBH36TE020R2	FBL36TE020R2				
25	FBV36TE025R2	FBN36TE025R2	FBH36TE025R2	FBL36TE025R2				
30	FBV36TE030R2	FBN36TE030R2	FBH36TE030R2	FBL36TE030R2				
35	FBV36TE035R2	FBN36TE035R2	FBH36TE035R2	FBL36TE035R2				
40	FBV36TE040R2	FBN36TE040R2	FBH36TE040R2	FBL36TE040R2				
45	FBV36TE045R2	FBN36TE045R2	FBH36TE045R2	FBL36TE045R2				
50	FBV36TE050R2	FBN36TE050R2	FBH36TE050R2	FBL36TE050R2				
60	FBV36TE060R2	FBN36TE060R2	FBH36TE060R2	FBL36TE060R2				
70	FBV36TE070R2	FBN36TE070R2	FBH36TE070R2	FBL36TE070R2				
80	FBV36TE080R2	FBN36TE080R2	FBH36TE080R2	FBL36TE080R2				
90	FBV36TE090R2	FBN36TE090R2	FBH36TE090R2	FBL36TE090R2				
100	FBV36TE100R2	FBN36TE100R2	FBH36TE100R2	FBL36TE100R2				

### FC, 1-Pole

AMPERE RATING	UL489 IC Rating @ 480V					TYPICAL	Spectra Bolt-On Mounting Kit	
	25KA	35KA	65KA	100KA	150KA		Terminal Lug	3-POLE
15	FCS16TE015R2	FCV16TE015R2	FCN16TE015R2	FCH16TE015R2	FCL16TE015R2	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6FDB Filler Plate - AFP3FDD	<b>Dual Mounted</b> Mounting Kit - AMCB4FDB Filler Plate - AFP3FDD
20	FCS16TE020R2	FCV16TE020R2	FCN16TE020R2	FCH16TE020R2	FCL16TE020R2			
25	FCS16TE025R2	FCV16TE025R2	FCN16TE025R2	FCH16TE025R2	FCL16TE025R2			
30	FCS16TE030R2	FCV16TE030R2	FCN16TE030R2	FCH16TE030R2	FCL16TE030R2			
35	FCS16TE035R2	FCV16TE035R2	FCN16TE035R2	FCH16TE035R2	FCL16TE035R2			
40	FCS16TE040R2	FCV16TE040R2	FCN16TE040R2	FCH16TE040R2	FCL16TE040R2			
45	FCS16TE045R2	FCV16TE045R2	FCN16TE045R2	FCH16TE045R2	FCL16TE045R2			
50	FCS16TE050R2	FCV16TE050R2	FCN16TE050R2	FCH16TE050R2	FCL16TE050R2			
60	FCS16TE060R2	FCV16TE060R2	FCN16TE060R2	FCH16TE060R2	FCL16TE060R2			
70	FCS16TE070R2	FCV16TE070R2	FCN16TE070R2	FCH16TE070R2	FCL16TE070R2			
80	FCS16TE080R2	FCV16TE080R2	FCN16TE080R2	FCH16TE080R2	FCL16TE080R2			
90	FCS16TE090R2	FCV16TE090R2	FCN16TE090R2	FCH16TE090R2	FCL16TE090R2			
100	FCS16TE100R2	FCV16TE100R2	FCN16TE100R2	FCH16TE100R2	FCL16TE100R2			

## Record Plus (Cont.)

### FC, 2-Pole

UL489 IC Rating @ 480V

Terminal Lug

Spectra Bolt-On Mounting Kit

AMPERE RATING	25KA	35KA	65KA	100KA	150KA	TYPICAL	3-POLE	2-POLE
15	FCS26TE015R2	FCV26TE015R2	FCN26TE015R2	FCH26TE015R2	FCL26TE015R2	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6FDB Filler Plate - AFP3FDD	<b>Dual Mounted</b> Mounting Kit - AMCB4DB Filler Plate - AFP3FDD
20	FCS26TE020R2	FCV26TE020R2	FCN26TE020R2	FCH26TE020R2	FCL26TE020R2			
25	FCS26TE025R2	FCV26TE025R2	FCN26TE025R2	FCH26TE025R2	FCL26TE025R2			
30	FCS26TE030R2	FCV26TE030R2	FCN26TE030R2	FCH26TE030R2	FCL26TE030R2			
35	FCS26TE035R2	FCV26TE035R2	FCN26TE035R2	FCH26TE035R2	FCL26TE035R2			
40	FCS26TE040R2	FCV26TE040R2	FCN26TE040R2	FCH26TE040R2	FCL26TE040R2			
45	FCS26TE045R2	FCV26TE045R2	FCN26TE045R2	FCH26TE045R2	FCL26TE045R2			
50	FCS26TE050R2	FCV26TE050R2	FCN26TE050R2	FCH26TE050R2	FCL26TE050R2			
60	FCS26TE060R2	FCV26TE060R2	FCN26TE060R2	FCH26TE060R2	FCL26TE060R2			
70	FCS26TE070R2	FCV26TE070R2	FCN26TE070R2	FCH26TE070R2	FCL26TE070R2			
80	FCS26TE080R2	FCV26TE080R2	FCN26TE080R2	FCH26TE080R2	FCL26TE080R2			
90	FCS26TE090R2	FCV26TE090R2	FCN26TE090R2	FCH26TE090R2	FCL26TE090R2			
100	FCS26TE100R2	FCV26TE100R2	FCN26TE100R2	FCH26TE100R2	FCL26TE100R2			

### FC, 3-Pole

UL489 IC Rating @ 480V

Terminal Lug

Spectra Bolt-On Mounting Kit

AMPERE RATING	25KA	35KA	65KA	100KA	150KA	TYPICAL	3-POLE	2-POLE
15	FCS36TE015R2	FCV36TE015R2	FCN36TE015R2	FCH36TE015R2	FCL36TE015R2	Load Side Included	<b>Dual Mounted</b> Mounting Kit - AMCB6FDB Filler Plate - AFP3FDD	N/A
20	FCS36TE020R2	FCV36TE020R2	FCN36TE020R2	FCH36TE020R2	FCL36TE020R2			
25	FCS36TE025R2	FCV36TE025R2	FCN36TE025R2	FCH36TE025R2	FCL36TE025R2			
30	FCS36TE030R2	FCV36TE030R2	FCN36TE030R2	FCH36TE030R2	FCL36TE030R2			
35	FCS36TE035R2	FCV36TE035R2	FCN36TE035R2	FCH36TE035R2	FCL36TE035R2			
40	FCS36TE040R2	FCV36TE040R2	FCN36TE040R2	FCH36TE040R2	FCL36TE040R2			
45	FCS36TE045R2	FCV36TE045R2	FCN36TE045R2	FCH36TE045R2	FCL36TE045R2			
50	FCS36TE050R2	FCV36TE050R2	FCN36TE050R2	FCH36TE050R2	FCL36TE050R2			
60	FCS36TE060R2	FCV36TE060R2	FCN36TE060R2	FCH36TE060R2	FCL36TE060R2			
70	FCS36TE070R2	FCV36TE070R2	FCN36TE070R2	FCH36TE070R2	FCL36TE070R2			
80	FCS36TE080R2	FCV36TE080R2	FCN36TE080R2	FCH36TE080R2	FCL36TE080R2			
90	FCS36TE090R2	FCV36TE090R2	FCN36TE090R2	FCH36TE090R2	FCL36TE090R2			
100	FCS36TE100R2	FCV36TE100R2	FCN36TE100R2	FCH36TE100R2	FCL36TE100R2			

## Record Plus (Cont.)

### FE, 2-Pole

UL489 IC Rating @ 480V		Terminal Lug		Spectra Bolt-On Mounting Kit	
FRAME AMPS	65KA	100KA	TYPICAL	3-POLE	2-POLE
25	FEN24DB025KF	FEH24DB025KF	FCALK15 (Order 1 lug kit)	<b>Dual Mounted</b> Mounting Kit - AMCB6FEB Filler Plate - AFP3FED	<b>Dual Mounted</b> Mounting Kit - AMCB4FEB Filler Plate - AFP3FED
60	FEN24DB060KF	FEH24DB060KF			
125	FEN24DB125KF	FEH24DB125KF			
150	FEN24DB150KF	FEH24DB150KF	FCALK16	<b>Single Mounted</b> Mounting Kit - AMCB3FEM Filler Plate - AFP3FES	<b>Single Mounted</b> Mounting Kit - AMCB2FEM Filler Plate - AFP3FES
250	FEN24DB250KF	FEH24DB250KF			

### FE, 3-Pole

UL489 IC Rating @ 480V		Terminal Lug		Spectra Bolt-On Mounting Kit	
FRAME AMPS	65KA	100KA	TYPICAL	3-POLE	2-POLE
25	FEN34DB025KF	FEH34DB025KF	FCALK15 (Order 1 lug kit)	<b>Dual Mounted</b> Mounting Kit - AMCB6FEB Filler Plate - AFP3FED	N/A
60	FEN34DB060KF	FEH34DB060KF			
125	FEN34DB125KF	FEH34DB125KF			
150	FEN34DB150KF	FEH34DB150KF	FCALK16	<b>Single Mounted</b> Mounting Kit - AMCB3FEM Filler Plate - AFP3FES	
250	FEN34DB250KF	FEH34DB250KF			

### FG, 2-Pole

UL489 IC Rating @ 480V				Terminal Lug		Spectra Bolt-On Mounting Kit	
FRAME AMPS	65KA	100KA	150KA	200KA	TYPICAL	3-POLE	2-POLE
250	FGN26DB250LF	FGH26DB250LF	FGL26DB250LF	FGP26DB250LF	FCALK15 (Order 1 lug kit)	<b>Dual Mounted</b> Mounting Kit - AMCB6FGB Filler Plate - AFP4FGD	<b>Dual Mounted</b> Mounting Kit - AMCB4FGB Filler Plate - AFP4FGD
400	FGN26DB400LF	FGH26DB400LF	FGL26DB400LF	FGP26DB400LF			
600	FGN26DB600LF	FGH26DB600LF	FGL26DB600LF	FGP26DB600LF			
						<b>Single Mounted</b> Mounting Kit - AMCB3FGM Filler Plate - AFP4GS	<b>Single Mounted</b> Mounting Kit - AMCB2FGM Filler Plate - AFP4GS

### FG, 3-Pole

UL489 IC Rating @ 480V				Terminal Lug		Spectra Bolt-On Mounting Kit	
FRAME AMPS	65KA	100KA	150KA	200KA	TYPICAL	3-POLE	2-POLE
250	FGN36DB250LF	FGH36DB250LF	FGL36DB250LF	FGP36DB250LF	FCALK15 (Order 1 lug kit)	<b>Dual Mounted</b> Mounting Kit - AMCB6FGB Filler Plate - AFP4FGD	N/A
400	FGN36DB400LF	FGH36DB400LF	FGL36DB400LF	FGP36DB400LF			
600	FGN36DB600LF	FGH36DB600LF	FGL36DB600LF	FGP36DB600LF			
						<b>Single Mounted</b> Mounting Kit - AMCB6FGB Filler Plate - AFP4FGS	

## Filler Plates Plug-In or Bolt-On Spectra™

Use to cover unused spaces. Includes filler plate support brackets and hardware.

SPACE X HEIGHT <sup>1</sup>	BOX WIDTH RANGE	SWITCHBOARD SECTION WIDTHS	PRODUCT NUMBER
1X	27", 31"	35"	APP1S
2X	27", 31"	35"	APP2S
3X	27", 31"	35"	APP3S
4X	27", 31"	35"	APP4S
5X	27", 31"	35"	APP5S
6X	27", 31"	35"	APP6S
1X	36", 40"	40"	APP1
2X	36", 40"	40"	APP2
3X	36", 40"	40"	APP3
4X	36", 40"	40"	APP4
5X	36", 40"	40"	APP5
6X	36", 40"	40"	APP6
1X	44"	45"	APP1W
2X	44"	45"	APP2W
3X	44"	45"	APP3W
4X	44"	45"	APP4W
5X	44"	45"	APP5W
6X	044"	45"	APP6W

<sup>1</sup> X-HEIGHT: 1X = 1 3/8"