



Top View




Knockouts

G=	1/2", 3/4", 1" KO
B=	1", 1-1/4", 1-1/2" KO
D=	3/4", 1", 1-1/4" KO
H=	9/32" KO


Left Side View




Front View Interior




Front View Inside Cover




Front View External Covers



Right Side View



Bottom View



Wire Range Size

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRAND	SOLID	STRAND
LINE	14-8	14-2	12-8	12-2
LOAD	14-10	14-10	---	---
NEUTRAL END HOLE	14-8	14-2	12-8	12-2
NEUTRAL SIDE HOLE	14-8	14-4	12-8	12-4
EQUIP. GRND.	12-8	12-2	12-8	12-2



Industrial Solutions

by ABB

RV EQUIP- 100A - MLO - RING TYPE - 30A & 20A RECEPT SURFACE MOUNT - SINGLE SIDE - UNLIGHTED - N3R - G90

CAT NO	DWG DATE	REV#
GE1LM032SS	04/07/2020	02