



### Top View




### Knockouts

G=	1/2", 3/4", 1" KO
B=	1", 1-1/4", 1-1/2" KO
D=	3/4", 1", 1-1/4" KO
H=	9/32" KO


### Left Side View




### Front View Interior




### Front View Inside Cover




### Front View External Covers



### Right Side View



### Bottom View



### Wire Range Size

CONNECTOR	COPPER		ALUMINUM		
	SOLID	STRAND	SOLID	STRAND	
LINE	14-8	14-2	12-8	12-2	
LOAD	14-10	14-10	---	---	
NEUTRAL	END HOLE	14-8	14-2	12-8	12-2
NEUTRAL	SIDE HOLE	14-8	14-4	12-8	12-4
EQUIP. GRND.		12-8	12-2	12-8	12-2



Industrial Solutions

by ABB

RV EQUIP- 100A - MLO - RING TYPE - 50A & 20A RECEPT SURFMOUNT-SINGLE SIDE-UNLIGHTED-N3R-G90

CAT NO	DWG DATE	REV#
GE1LM502SS	04/07/2020	02