




Left Side View




Front View Interior




Front View External Covers




Front Exterior View



Right Side View



Bottom View



Knockouts

- G= 1/2", 3/4", 1" KO
- B= 1", 1-1/4", 1-1/2" KO
- D= 3/4", 1", 1-1/4" KO
- H= 9/32" KO

Wire Range Size

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRAND	SOLID	STRAND
LINE	---	6-1/0	---	6-1/0
LOAD	14-10	14-10	---	---
NEUTRAL	LARGE HOLE 12-8	12-1/0	10-8	10-1/0
NEUTRAL	SMALL HOLE 14-8	14-4	12-8	12-4
EQUIP. GRND.	12-8	12-2	12-8	12-2



Industrial Solutions

by ABB

RV EQUIP-100A-MLO-RING TYPE-50A,30A&20A
RECEPT-SURFACE-SINGLE SIDED-UNLIGHTED-G90-N3R

CAT NO	DWG DATE	REV#
GE1LM532SS	04/07/2020	02