



Top View




Knockouts

H=	9/32" KØ
G=	1/2", 3/4", 1" KØ
B=	1", 1-1/4", 1-1/2" KØ
D=	3/4", 1", 1-1/4" KØ


Left Side View




Front View Interior




Front View Inside Cover




Front View External Cover



Right Side View



Bottom View



Wire Range Size

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRAND	SOLID	STRAND
LINE	14-8	14-1/0	12-8	12-1/0
LOAD	14-10	14-10	---	---
NEUTRAL END HOLE	14-8	14-2	12-8	12-2
NEUTRAL SIDE HOLE	14-8	14-4	12-8	12-4
EQUIP. GRND.	12-8	12-2	12-8	12-2

NOTES:
LUG TYPE IS LOOP FEED

	Industrial Solutions	by ABB
RV EQUIP- 100A - MLO - UNMETERED - 30A&20A RECEPT SURFACE MOUNT- SINGLE SIDE - UNLIGHTED - N3R - G90		
CAT NO	DWG DATE	REV#
GE1LU032SS	04/07/2020	02