



Knockouts

S= 1/2", 3/4", 1", 1-1/4", 1-1/2" K□
G= 1/2", 3/4", 1" K□

Left Side View




Front View Interior




Front View Inside Cover


Front View External Cover



Right Side View



Bottom View



Wire Range Size

CONNECTOR	COPPER		ALUMINUM		
	SOLID	STRAND	SOLID	STRAND	
LINE	14-8	14-2	12-8	12-2	
LOAD	14-10	14-10	---	---	
NEUTRAL	END HOLE	14-8	14-2	12-8	12-2
NEUTRAL	SIDE HOLE	14-8	14-4	12-8	12-4
EQUIP. GRND.	12-8	12-2	12-8	12-2	



Industrial Solutions

by ABB

RV EQUIP- 100A - MLO - UNMETERED - 50A&20A RECEPT SURFACE MOUNT- SINGLE SIDE - UNLIGHTED - N3R - G90

CAT NO	DWG DATE	REV#
GE1LU502SS	04/07/2020	02