


Top View




Front View Interior

100AMP, 5 CIRCUIT LOAD CENTER
50AMP, BREAKER 2-POLE
30AMP, BREAKER 1-POLE
20AMP, BREAKER 1-POLE

14-50R
50AMP.
RECEPTACLE
LOOP FEED LUG
TERMINAL BAR




Front View External Cover




5-20R2GFI
20AMP.
GFI DUPLEX
R32U
30AMP.
RECEPTACLE

Front View Exterior



Right Side View



Wire Range Size

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRAND	SOLID	STRAND
LINE	14-8	14-1/0	12-8	12-1/0
LOAD	14-10	14-10	---	---
NEUTRAL LARGE HOLE	12-8	12-1/0	10-8	10-1/0
NEUTRAL SMALL HOLE	14-8	14-4	12-8	12-4
POST LINE CONNECTORS SUITABLE FOR LOOP FEED	#6-350 KCMIL	KCMIL	#6-350 KCMIL	
EQUIP. GRND. POST	14-2/0	14-2/0	14-2/0	14-2/0

NOTES: EARTH BURIAL POST

	Industrial Solutions	by ABB
RV EQUIP-100A-MLO-UNMETERED-50/30A/20A RECEPT EARTH BURIAL POST-BACK TO BACK-UNLIGHTED-N3R-G90		
CAT NO	DWG DATE	REV#
GE1LU532EB	04/07/2020	02