



GEH4692

Neutral Kit

TNI21



Hazards of electrical shock or burn! Turn off power before working inside this equipment.

Used with:

240 Volt 30 Amp Heavy and General Switches.

Description:

This device, catalog number TNI21, Model 1, is UL listed for use as 240Volt maximum insulated groundable neutral. The complete kit consists of the following parts:

Neutral Block with:

- 1 each lug for use with #14-8 copper wire or #12-8 aluminum wire (for grounding)
- 1 each mounting screw

For bonding:

- 1 each #10-32UNF X 7/8" self-threading bonding screw

Installation

Install neutral in enclosure on the switch base with the mounting screw.

When installing wiring, the following lug screw torques are recommended. Torque from 36-40 in-lbs.

Bonding

If bonding is required, insert bonding screw provided through the hole in the switch enclosure, penetrating the insulator.

—
TNI21 Neutral Kit

