



POWER TERMINALS:
 SIZE 0-1 #8 AWG MAX, #14 AWG MIN.
 SIZE 2 #4 AWG MAX, #14 AWG MIN.

CR309 Open NEMA Sizes 0-2 Two-Speed

NEMA Size	Operation Type	Dimension A	Dimension B	Dimension C	Dimension D	Dimension E	Mounting Screw Size	Shipping Weight (lbs.)
0, 1	Two-Speed, Two-Winding	7.00 (177.8)	8.88 (225.6)	3.94 (100.0)	6.50 (165.1)	4.44 (112.8)	#10	8
0, 1	Two-Speed, One-Winding	7.00 (177.8)	9.88 (251.0)	3.94 (100.0)	6.50 (165.1)	4.44 (112.8)	#10	8 3/4
2	Two-Speed, Two-Winding	9.12 (231.6)	10.36 (263.2)	5.38 (136.6)	8.50 (215.8)	5.19 (131.7)	1/4"	18 1/4
2	Two-Speed, One-Winding	9.12 (231.6)	13.38 (339.6)	5.38 (136.6)	8.50 (215.8)	5.19 (131.7)	1/4"	19

Dual Dimensions $\frac{\text{Inches}}{\text{Millimeters}}$ (Estimating Only)



PUB# GEP1260-01-033

Open Type, NEMA Sizes 0-2 Two-Speed

File Name 309 Sz0-2 2Spd NonCombo FVR Str Open	Date 06/01/2010	Rev 01
--	--------------------	-----------