


CR309 NEMA Type 1 NEMA Sizes 0-2 Two-Speed

NEMA Size (lbs.)	Operation Type	Dimension A	Dimension B	Dimension C	Dimension D	Dimension E	Mounting Screw Size	Shipping Weight
0, 1	Two-Speed, Two-Winding	10.00 (254.0)	10.00 (254.0)	4.62 (117.3)	8.00 (203.2)	8.00 (203.2)	#10	13
0, 1	Two-Speed, One-Winding	10.00 (254.0)	13.50 (342.9)	4.62 (117.3)	8.00 (203.2)	11.50 (292.1)	#10	14
2	Two-Speed, Two-Winding	13.25 (336.6)	12.00 (304.8)	6.12 (155.4)	11.00 (279.4)	9.00 (228.6)	1/4"	28
2	Two-Speed, One-Winding	13.25 (336.6)	16.00 (406.4)	6.12 (155.4)	11.00 (279.4)	13.00 (330.2)	1/4"	30

Dual Dimensions  $\frac{\text{Inches}}{\text{Millimeters}}$  (Estimating Only)



PUB# GEP1260-01-036

NEMA Type 1, Sizes 0-2 Two-Speed

File Name  
309 Sz0-2 2Spd NonCombo FVRStr  
Type1

Date  
06/01/2010

Rev  
01