


**CR309 NEMA Type 12 NEMA Sizes 0-2 Two-Speed**

NEMA Size	Operation Type	Dimension A	Dimension B	Dimension C	Dimension D	Dimension E	Dimension F	Shipping Weight (lbs.)
0, 1	Two-Speed, Two-Winding	11.62 (295.1)	10.25 (260.4)	4.75 (120.6)	11.00 (279.4)	7.00 (177.8)	10.25 (260.4)	14
0, 1	Two-Speed, One-Winding	15.62 (396.7)	14.25 (362.0)	4.75 (120.6)	15.00 (381.0)	11.00 (279.4)	14.25 (362.0)	14
2	Two-Speed, Two-Winding	14.62 (371.3)	12.25 (311.2)	6.25 (158.8)	14.00 (355.6)	9.00 (228.6)	13.25 (336.6)	30
2	Two-Speed, One-Winding	17.62 (447.5)	16.25 (412.8)	6.25 (158.8)	17.00 (431.8)	12.00 (304.8)	16.25 (412.8)	30

Dual Dimensions  $\frac{\text{Inches}}{\text{(Millimeters)}}$  (Estimating Only)



PUB# GEP1260-01-038

NEMA Type 12, Sizes 0-2 Two-Speed

File Name  
309 Sz0-2 2Spd NonCombo FVRStr  
Type12

Date  
06/01/2010

Rev  
01