



### NEMA Type 3R/12 Enclosure

(Enclosure Code = 6 or 2)

NEMA Size	A	B	C	D	E	F	G	H (dia)	J (dia)	K (dia)
0-2	20.00 (508.0)	33.25 (844.6)	8.20 (208.2)	3.48 (88.5)	1.91 (48.5)	8.00 (203.2)	32.13 (816.0)	0.34 (8.7)	0.41 (10.3)	0.81 (20.6)
3-4	23.00 (584.2)	53.82 (1367.0)	8.20 (208.2)	3.50 (88.8)	3.41 (86.6)	8.00 (203.2)	52.70 (1338.5)	0.34 (8.7)	0.41 (10.3)	0.81 (20.6)

Dual Dimensions  $\frac{\text{Inches}}{\text{(Millimeters)}}$  (Estimating Only)



PUB# GEP1260-01-057

NEMA Type 3R/12 Enclosure

File Name	Date	Rev
410 411 490 Sz0-4 FVR ComboStr Type3R_12	06/01/2010	01