



NEMA Type 4/4X Enclosure

(Enclosure Code = 4)

NEMA Size	A	B	C	D	E	F	G	H (dia)	J (dia)	K (dia)
0-2	20.00 (508.0)	33.32 (846.3)	8.14 (206.7)	3.72 (94.6)	1.91 (48.5)	8.00 (203.2)	32.20 (817.8)	0.34 (8.7)	0.41 (10.3)	0.81 (20.6)
3-4	23.00 (584.2)	53.76 (1365.5)	8.14 (206.7)	3.55 (90.2)	3.41 (86.6)	8.00 (203.2)	52.64 (1336.9)	0.34 (8.7)	0.41 (10.3)	0.81 (20.6)

Dual Dimensions $\frac{\text{Inches}}{\text{(Millimeters)}}$ (Estimating Only)



PUB# GEP1260-01-058

NEMA Type 4/4X Enclosure

File Name
410 411 490 Sz 0-4 FVR Combo Str
Type4_4X

Date
06/01/2010

Rev
01