


NEMA Type 3R/12 Enclosure

(Enclosure Code = 6 or 2)

NEMA Size	A	B	C	D	E	F	G	H (dia)	J (dia)	K (dia)
0-2	20.00 (508.0)	33.25 (844.6)	8.20 (208.2)	3.48 (88.5)	1.91 (48.5)	8.00 (203.2)	32.13 (816.0)	0.34 (8.7)	0.41 (10.3)	0.81 (20.6)
3-4	23.00 (584.2)	53.82 (1367.0)	8.20 (208.2)	3.50 (88.8)	3.41 (86.6)	8.00 (203.2)	52.70 (1338.5)	0.34 (8.7)	0.41 (10.3)	0.81 (20.6)

Dual Dimensions $\frac{\text{Inches}}{\text{(Millimeters)}}$ (Estimating Only)

 imagination at work		
PUB# GEP1260-01-062		
CR412, CR413, CR492, CR414, CR415, CR494 Magnetic Starters		
File Name 412-415, 492, 494 Sz 0-4 2Spd Combo Str Type 3R/12	Date 06/01/2010	Rev 01