



GE Consumer & Industrial -
Electrical Distribution

Current Ratings

10, 15, 20, 25, 30, 35, 40, 45, 50, 60, 70,
80, 90 and 100 Amperes

Voltage Ratings

240 Vac, (125/250 Vdc)

Frequency Rating

60 Hertz

**Molded Case Circuit Breaker
E 100 LINE**

**Type TE
Long-time Delay and Instantaneous
Time-current Curves**

Curves show enclosure-compensated circuit breaker
in open air, 40°C ambient, wired with conductors of
corresponding rating, no prior load. For all other
ambients, use shift index at top of sheet.

GES-6107C

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.