



GE Consumer & Industrial -
Electrical Distribution

Current Ratings

250, 300, 350 and 400 Amperes

Voltage Ratings

2- and 3-pole - 240 Vac (250 Vdc)

Frequency Ratings

Dc or 50/60 Hertz

**Molded Case Circuit Breaker
J-600 Line**

Type TJD (400 Amps Max.)
Long-time Delay and Instantaneous
Time-current Curves

Curves show ambient-compensated circuit breaker in open air, 10-50°C, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

GES-6112A

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.