



MULTIPLES OF CURRENT RATING

GENERAL ELECTRIC

Current Ratings
3000A Frame — 2000, 2500 and 3000 amperes
4000A Breaker — 4000 amperes

Voltage Ratings
600 volts a-c, 250 volts d-c

Frequency Rating
60 Hertz

MOLDED-CASE CIRCUIT BREAKER
POWER BREAK™
Type THS (3000A Frame & 4000A Breaker)

Long-time Delay, Short-time Delay and Instantaneous Time-current Curves
(Curves show circuit breaker in open air, 0-50 C ambient, wired with conductors of corresponding rating, no prior load.)

GES-6132A

Adjustments
Standard long-time magnetic delay, 100% of rating, not adjustable. Optional THS adjustable trip, 70-100% of rating.
Short-time magnetic delay, adjustable pickup as indicated by blocks shown for each setting. Instantaneous magnetic trip, fixed 42,000 sym amperes irrespective of trip unit rating.