



GE Consumer & Industrial -  
Electrical Distribution

**Current Ratings**

15, 20, 25, 30, 35, 40, 45 and 50 Amperes

**Voltage Ratings**

1- and 2- pole - 120/240 Vac  
2- and 3- pole - 240 Vac

**Frequency Ratings**

50/60 Hertz

**Molded Case Circuit Breakers  
"Q" Line**

Types THQL, THQB, THQC, THHQL,  
THHQB, THHQC, TXQL, TXQB, TXQC  
(30 Amps Max.)

**Long-time Delay and Instantaneous  
Time-current Curves**

Curves show circuit breaker in open air, 40°C  
ambient, wired with conductors of corresponding  
rating, no prior load. For all other ambients, use  
rating shift index at top of sheet.

**GES-6202A**

**Adjustments**

Long-time delay thermal trip: not adjustable.  
Instantaneous magnetic trip: not adjustable.