



GE Industrial Solutions

Current Ratings

2- and 3- pole – 60, 70, 80, 90 and 100 Amperes
1- pole – 60 and 70 Amperes
2- pole 110 and 125 Amperes (120/240 Vac)

Voltage Ratings

1- and 2- pole – 120/240 Vac
2- and 3- pole – 240 Vac

Frequency Ratings

50/60 Hertz

**Molded Case Circuit Breakers
"Q" Line**

Types THQL, THQB, THQC, THHQL, THHQB, THHQC

Ambient Compensated
Long-time Delay and Instantaneous
Time-current Curves

Curves show ambient-compensated circuit breaker in open air, 10°C to 50°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

GES-6203B

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.