



GE Consumer & Industrial -
Electrical Distribution

Current Ratings

125, 150, 175 and 200 Amperes

Voltage Ratings

2- pole - 120/240 Vac

Frequency Rating

60 Hertz

**Molded Case Circuit Breakers
"Q" Line**

Types TQDL, THQDL
Long-time Delay and Instantaneous
Time-current Curves

Curves show circuit breaker in open air, 40°C
ambient, wired with conductors of corresponding
rating, no prior load. For all other ambients,
use rating shift index at top of sheet.

GES-6206B

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.