



**GE Consumer & Industrial -
Electrical Distribution**

Current Ratings

3, 7, 15 and 30 Amperes

Voltage Ratings

240, 480, 600 Vac

Frequency Rating

50/60 Hertz

**Current-Limiting Mag-Break®
Motor Circuit Protector**

Type TEML

Instantaneous Time-current Curves

GES-6232

Adjustments

Instantaneous magnetic trip: continuously adjustable.

Note 1: Current limiting range, breaker totally clears prior to 0.01 sec. For additional data refer to I_p and I²T curves.