



GE Consumer & Industrial -
Electrical Distribution

Current Ratings

60, 70, 80, 90 and 100 Amperes

Voltage Ratings

2- and 3- pole - 120/240 Vac

Frequency Ratings

50/60 Hertz

Molded Case Circuit Breakers

Type TMQD, 60-100 Amperes
Enclosure Compensated
Long-time Delay and Instantaneous
Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

GES-6240

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.