



GE Consumer & Industrial -  
Electrical Distribution

**Current Ratings**  
15 and 20 Amperes

**Voltage Ratings**  
1-pole and 2-pole - 120/240 Vac  
2-pole and 3-pole - 240 Vac

**Frequency Ratings**  
50/60 Hertz

### Molded Case Circuit Breakers Q Line

Types THQB, THQC, THHQB, THHQC,  
(MOD C & MOD S)  
Long-time Delay and Instantaneous  
Time-current Curves

Curves show circuit breaker in open air, 40°C  
ambient, wired with conductors of  
corresponding rating, no prior load. For all other  
ambients, use rating shift index at top of sheet.

## GES-9885

#### Adjustments

Long-time delay thermal trip: not adjustable.  
Instantaneous magnetic trip: not adjustable.