



GE Consumer & Industrial -
Electrical Distribution

Current Ratings
20 Amperes

Voltage Ratings
1-pole and 2-pole - 120/240 Vac

Frequency Ratings
50/60 Hertz

Molded Case Circuit Breakers Q Line

Types THQL, THQLT, THQLQ, THQP, THHQL,
THQB___LM and THHQB___LM
(MOD C & MOD S)
Long-time Delay and Instantaneous
Time-current Curves

Curves show circuit breaker in open air, 40°C
ambient, wired with conductors of
corresponding rating, no prior load. For all other
ambients, use rating shift index at top of sheet.

GES-9887B

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.