



GE Consumer & Industrial -
Electrical Distribution

Current Ratings

25, 30, 35, 40, 45 and 50 Amperes

Voltage Ratings

1-pole and 2-pole - 120/240 Vac
2-pole and 3-pole - 240 Vac

Frequency Ratings

50/60 Hertz

**Molded Case Circuit Breakers
Q Line**

Types THQL, THQLT, THQLQ, THQB,
THQC, THQP, THHQL, THHQB, THHQC,
TXQL, TXQB, TXQC

**Long-time Delay and Instantaneous
Time-current Curves**

Curves show circuit breaker in open air,
40°C ambient, wired with conductors of
corresponding rating, no prior load. For all other
ambients, use rating shift index at top of sheet.

GES-9888

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.