



Industrial Solutions

Current Ratings

15, 20, 25 and 30 Amperes

Voltage Ratings

1-pole – 277 Vac (125 Vdc)

2- and 3- pole – 480 Vac (250 Vdc)

Frequency Ratings

60 Hertz

Molded Case Circuit Breaker

Type TEY,TEYF and TEYRC 15-30 Amperes

Enclosure Compensated Long-time Delay and Instantaneous Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

GES6237

Adjustments

Long-time delay thermal trip: not adjustable.

Instantaneous magnetic trip: not adjustable.

by **ABB**