



GE Consumer & Industrial -  
Electrical Distribution

**Current Ratings**  
15, 20 and 30 Amperes

**Voltage Ratings**  
600 Vac (250 Vdc)

**Frequency Rating**  
Dc or 60 Cycles

**Integrally Fused  
Molded Case Circuit Breaker  
TRI-BREAK® LINE**

Type TB1 (15-30 Amperes)  
Thermal Trip, Magnetic Trip and  
Current Limiter Characteristics

Time vs. RMS Current

**K215-71D**

**Adjustments**  
Long-time delay thermal trip: not adjustable.  
Instantaneous magnetic trip: not adjustable.