



GE Consumer & Industrial -
Electrical Distribution

Current Ratings

40, 50, 70, 90, and 100 Amperes

Voltage Ratings

600 Vac (250 Vdc)

Frequency Rating

Dc or 60 Cycles

**Integrally Fused
Molded Case Circuit Breaker
TRI-BREAK® LINE**

Type TB1 (40-100 Amperes)
Thermal Trip, Magnetic Trip and
Current Limiter Characteristics

Time vs. RMS Current

K215-72C

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.