



GE Consumer & Industrial -  
Electrical Distribution

**Current Ratings**

15, 20, 25, 30, 35, 40, 45 and 50 Amperes

**Voltage Ratings**

1 Pole 240 Vac  
2 and 3 pole - 415 Vac

**Frequency Ratings**

50/60 Hertz

**Molded Case Circuit Breaker  
E 100 LINE**

Type TEB  
1, 2 and 3 Pole - 15 to 50 Amperes  
Long-time Delay and Instantaneous  
Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use shift index at top of sheet.

**K215-96A**

**Adjustments**

Long-time delay thermal trip: not adjustable.  
Instantaneous magnetic trip: not adjustable.