




Top View




Configuration




Left Side View





Front View Interior



Front View Inside Cover




Front View External



Wire Range Size

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRAND	SOLID	STRAND
LINE	---	6-1/0	---	6-1/0
LOAD	14-10	14-10	---	---
NEUTRAL <small>LARGE HOLE</small>	12-8	12-1/0	10-8	10-1/0
NEUTRAL <small>SMALL HOLE</small>	14-8	14-4	12-8	12-4
EQUIP. GRND.	12-8	12-2	12-8	12-2

Bottom View



Knockouts

- G= 1/2", 3/4", 1" KØ
- B= 1", 1-1/4", 1-1/2" KØ
- D= 3/4", 1", 1-1/4" KØ
- H= 9/32" KØ

Receptacles

(2) BR54U
5-20R2GFCI

Circuit Protection

(2) THQL2150
THQL1120



MIDWEST RV EQUIP METALLIC 100A SURFACE RING MTR
(2)50/20A GFI RECPT 120V 1PH3W UL LISTED G90 N3R

CAT NO	DWG DATE	REV #
M004C010	04/10/2017	01