### **Top View**

**Front View** 

Interior

#### 1-1/2" HUB HOLE 1.5 3.8


**Front View** 

**Inside Cover** 

#### **Knockouts**

G= 1/2', 3/4', 1' KD B= 1", 1-1/4", 1-1/2" KD D= 3/4", 1", 1-1/4" KD H= 9/32' KD

# Configuration




# **Right Side**


View



#### Left Side View



#### **Front View** Exterior #1



**Front View** 

Exterior # 2


# **Receptacles**

BR32U
5-20R2GFCI

#### **Circuit Protection**

THQL1130	
THQL1120	
SPACE THQL1120	

# **Bottom View**



#### Wire Range Size

CONNECTOR		COPPER		ALUMINUM	
		SOLID	STRAND	SOLID	STRAND
LINE		14-8	14-2	12-8	12-2
LOAD		14-10	14-10		
NEUTRAL	END HOLE	14-8	14-2	12-8	12-2
NEUTRAL	SIDE HOLE	14-8	14-4	12-8	12-4
EQUIP. GRND.		12-8	12-2	12-8	12-2



MIDWEST RV EQUIP METALLIC 100A SURFACE RING MTR 30/20A RECPT 120V 1PH3W UL LISTED G90 N3R

CAT NO	DWG DATE	REV#
M041C010	04/10/2017	01