




### Front Covers View




### Top View




### Front Interior View




### Bottom View



### Side View



### Configuration



### Knockouts

- F= 1/2" KO
- Y= 1-1/4", 1-1/2", 2", 2-1/2", 3" KO
- N= 1/2", 3/4", 1", 1-1/4", 1-1/2", 2" KO
- X= 1/2", 3/4", 1", 1-1/4", 1-1/2", 2", 2-1/2" KO

### Wire Range Size

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRANDED	SOLID	STRANDED
LINE	----	6-4/0	----	6-4/0
LOAD	----	1-4/0	----	1-4/0
NEUTRAL A	----	1-4/0	----	1-4/0
NEUTRAL/GRND. B	----	6-2/0	----	6-2/0
NEUTRAL/GRND. C	14-8	14-4	12-8	12-4

Midwest Electric Products  
Plainville, CT

MIDWEST SERVICE EQUIP 200A SURFACE MOUNT RING  
METERED OH/UG UL LISTED 120/240V 4 CKT N3R  
PARALLEL

CAT NO	DWG DATE	REV #
M282CB1	07/11/2016	01