



- NOTES:**
1. OPERATOR INTERFACE PANEL.
  2. MAIN INPUT CIRCUIT BREAKER.
  3. 1-8 (50-250A) SUBFEEDS.
  4. RECOMMEND A MINIMUM OF 30" IN REAR OR SIDE OF UNIT FOR MAINTENANCE.
  5. MINIMUM OF 18" CLEARANCE FOR DOOR SWING.
  6. RECOMMEND 6" CLEARANCE BETWEEN VENTILATED SIDES AND WALL FOR PROPER COOLING.



<p>THIS DRAWING CONTAINS CONFIDENTIAL &amp; PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF GENERAL ELECTRIC CO.</p>			
<p>TITLE GE ZENITH SERIES MDU, CLASSIC DESIGN 200-300kva (8) SUBFEED CBS</p>			
DWG. NUMBER	REVISION		
DWG11006-GE	A2		
DRAWN BY	CHECKED BY		
RAE	DMS		
DATE	DATE		
07-16-10	01-02-13		
			
<p>GE Critical Power</p>			