



Front View




Side View



Notes

- 1) FINISH: GRAY
- 2) CABINET: 16 GA GALV. STEEL
- 3) 125 AMP CONTINUOUS,
600 VAC, 1 PHASE, 3 WIRE
- 4) TEMPORARY CARDBOARD METER OPENING COVER PROVIDED
- 5) FOR AN EXPOSED INNER-TITE OR BROOKS STANDARD LENGTH
BARREL LOCK IN CONJUNCTION BROOKS LOCK GUARDS #865
OR #86505 WITH A PERMANENTLY WELDED BRACKET
- 6) MIDWEST LABEL ATTACHED TO THE END OF THE CARTON
- 7) MIDWEST LOGO LOCATED IN THE LOWER LEFT-HAND CORNER
OF THE FRONT
- 8) STACK FLAT ON 36 X 48 PALLET. (DO NOT STACK ON SIDES)

Bottom View



METER SOCKET-(1) 125A 600V 1P3W HUB OPN 4-TERM N3R
TRIPLX GRD G90 HORN BYP AEP BARREL LOCK TOP FEED

CAT NO	DWG DATE	REV #
MEPKS1AS1BTV	02/10/2016	01