



### Front View




### Left Side View



### Notes

- 1) FINISH: GRAY
- 2) CABINET: 16GA GALV. STEEL
- 3) 200 AMP CONTINUOUS  
600 VAC, 1 PHASE, 3 WIRE
- 4) FOR BROOKS OR INNER-TITE STANDARD LENGTH  
BARREL LOCK IN CONJUNCTION WITH BROOKS  
LOCK GUARDS #865 OR #86505 WITH A PERMANENTLY  
WELDED BRACKET.
- 5) MIDWEST LABEL ATTACHED TO THE END OF THE CARTON.
- 6) TEMPORARY CARDBOARD METER OPENING COVER PROVIDED.
- 7) MIDWEST LOGO LOCATED IN THE LOWER LEFT-HAND  
CORNER OF THE FRONT.
- 8) STACK FLAT ON 36 X 48 PALLET. ( DO NOT STACK ON SIDES )

### Bottom View



METER SOCKET - (1) 200A 600V 1P3W HUB OPN 4-TERM  
N3R TRIPLX GRD G90 HORN BYP AEP BARREL LK TOP FEED

CAT NO	DWG DATE	REV #
MEPKS1CS1BJTV	02/10/2016	01