


Midwest Safety Switch Quick Selection Guide



General Duty Safety Switches (240V & 600V) through 200A

Duty	Volts	Fusible or Non-Fusible	Poles	Amperage	Indoor Type 1 Enclosure	Outdoor Type 3R Enclosure	Neutral	Ground Lug Kit	Class R Fuse Kit
General	240V	Fusible	2	30	MGF221N	MGF221NR	Included	MGL2	MGR12
				60	MGF222N	MGF222NR	Included	MGL2	MGR22
				100	MGF223N	MGF223NR	Included	MGL4	MGR42
				200	MGF224N	MGF224NR	Included	MGL4	MGR42
			3	30	MGF321N	MGF321NR	Included	MGL2	MGR12
				60	MGF322N	MGF322NR	Included	MGL2	MGR22
				100	MGF323N	MGF323NR	Included	MGL4	MGR42
				200	MGF324N	MGF324NR	Included	MGL4	MGR42
	Non-Fusible	3	30	MGU321	MGU321R	MNK1	MGL2	-	
			60	MGU322 ¹	MGU322R ¹	-	MGL2	-	
			100	MGU323 ¹	MGU323R ¹	-	MGL4	-	
			200	MGU324	MGU324R	MNK4A	MGL4	-	

Proudly represented locally by:



Heavy Duty Safety Switches (240V & 600V) through 200A

Duty	Volts	Fusible or Non-Fusible	Poles	Amperage	Indoor Type 1 Enclosure	Outdoor Type 3R Enclosure	Neutral	Ground Lug Kit	Class R Fuse Kit	Auxiliary Contact Kits (1NO/1NC) (2NO/2NC)	
										MAUX61S	MAUX21D
Heavy	240V	Fusible	2	30	MHF221N	MHF221NR	Included	MGL2	MHR12	MAUX61S	MAUX21D
				60	MHF222N	MHF222NR	Included	MGL2	MHR22	-	MAUX64D
				100	MHF223N	MHF223NR	Included	MGL4	MHR46	-	MAUX64D
				200	MHF224N	MHF224NR	Included	MGL4	MHR46	-	MAUX64D
			3	30	MHF321N	MHF321NR	Included	MGL2	MHR16	MAUX61S	MAUX21D
				60	MHF322N	MHF322NR	Included	MGL2	MHR26	-	MAUX64D
				100	MHF323N	MHF323NR	Included	MGL4	MHR46	-	MAUX64D
				200	MHF324N	MHF324NR	Included	MGL4	MHR46	-	MAUX64D
	600V	Fusible	3	30	MHF361	MHF361R	MNK2	MGL2	MHR12	MAUX61S	MAUX21D
				60	MHF362	MHF362R	MNK2A	MGL2	MHR22	-	MAUX64D
				100	MHF363	MHF363R	MNK3A	MGL4	MHR46	-	MAUX64D
				200	MHF364	MHF364R	MNK4A	MGL4	MHR46	-	MAUX64D
		Non-Fusible	3	30	MHU321 ²	-	MNK1	MGL2	-	MAUX61S	MAUX21D
				30	MHU361	MHU361R	MNK2	MGL2	-	MAUX61S	MAUX21D
				60	MHU362	MHU362R	MNK2	MGL2	-	-	MAUX64D
				100	MHU363	MHU363R	MNK3A	MGL4	-	-	MAUX64D
			200	MHU364	MHU364R	MNK4A	MGL4	-	-	MAUX64D	



MGU321R



MGF322



MNX2



MGL4



MHR22



MAUX64



MHF363R



MHU324R

¹A neutral is not available. If one is required use Heavy Duty switch.

²240V max.

Midwest Safety Switch Cross Reference Guide



Midwest #	Eaton C-H	Siemens	SqD	Description
-----------	-----------	---------	-----	-------------

General Duty 240V-Fusible 2 Phase

MGF221N	DG221NGB	GF221N	D221N	30A GD DISC 2P FUSIBLE TYP1 240V
MGF221NR	DG221NRB	GF221NR	D221NRB	30A GD DISC 2P FUSIBLE TYP3R 240V
MGF222N	DG222NGB	GF222N	D222N	60A GD DISC 2P FUSIBLE TYP1 240V
MGF222NR	DG222NRB	GF222NR	D222NRB	60A GD DISC 2P FUSIBLE TYP3R 240V
MGF223N	DG223NGB	GF223N	D223N	100A GD DISC 2P FUSIBLE TYP1 240V
MGF223NR	DG223NRB	GF223NR	D223NRB	100A GD DISC 2P FUSIBLE TYP3R 240V
MGF224N	DG224NGK	GF224N	D224N	200A GD DISC 2P FUSIBLE TYP1 240V
MGF224NR	DG224NRK	GF224NR	D224NRB	200A GD DISC 2P FUSIBLE TYP3R 240V

General Duty 240V-Fusible 3 Phase

MGF321N	DG321NGB	GF321N	D321N	30A GD DISC 3P FUSIBLE TYP1 240V
MGF321NR	DG321NRB	GF321NR	D321NRB	30A GD DISC 3P FUSIBLE TYP3R 240V
MGF322N	DG322NGB	GF322N	D322N	60A GD DISC 3P FUSIBLE TYP1 240V
MGF322NR	DG322NRB	GF322NR	D322NRB	60A GD DISC 3P FUSIBLE TYP3R 240V
MGF323N	DG323NGB	GF323N	D323N	100A GD DISC 3P FUSIBLE TYP1 240V
MGF323NR	DG323NRB	GF323NR	D323NRB	100A GD DISC 3P FUSIBLE TYP3R 240V
MGF324N	DG324NGK	GF324N	D324N	200A GD DISC 3P FUSIBLE TYP1 240V
MGF324NR	DG324NRK	GF324NR	D324NRB	200A GD DISC 3P FUSIBLE TYP3R 240V

General Duty 240V-Non-Fusible 3 Phase

MGU321	DG221UGB	GNF321	DU321	30A GD DISC 3P NONFUSE TYP1 240V
MGU321R	DG221URB	GNF321R	DU321RB	30A GD DISC 3P NONFUSE TYP3R 240V
MGU322	DG222UGB	GNF322	DU322	60A GD DISC 3P NONFUSE TYP1 240V
MGU322R	DG222URB	GNF322R	DU322RB	60A GD DISC 3P NONFUSE TYP3R 240V
MGU323	DG223UGB	GNF323	DU323	100A GD DISC 3P NONFUSE TYP1 240V
MGU323R	DG223URB	GNF323R	DU323RB	100A GD DISC 3P NONFUSE TYP3R 240V
MGU324	DG224UGK	GNF324	DU324	200A GD DISC 3P NONFUSE TYP1 240V
MGU324R	DG224URK	GNF324R	DU324RB	200A GD DISC 3P NONFUSE TYP3R 240V

General Duty



Heavy Duty



Midwest #	Eaton C-H	Siemens	SqD	Description
-----------	-----------	---------	-----	-------------

Heavy Duty 240V-Fusible 2 Phase

MHF221N	DH221NGK	HF221N	H221N	30A HD DISC 2P FUSIBLE TYP1 240V
MHF221NR	DH221NRK	HF221NR	H221NRB	30A HD DISC 2P FUSIBLE TYP3R 240V
MHF222N	DH222NGK	HF222N	H222N	60A HD DISC 2P FUSIBLE TYP1 240V
MHF222NR	DH222NRK	HF222NR	H222NRB	60A HD DISC 2P FUSIBLE TYP3R 240V
MHF223N	DH223NGK	HF223N	H223N	100A HD DISC 2P FUSIBLE TYP1 240V
MHF223NR	DH223NRK	HF223NR	H223NRB	100A HD DISC 2P FUSIBLE TYP3R 240V
MHF224N	DH224NGK	HF224N	H224N	200A HD DISC 2P FUSIBLE TYP1 240V
MHF224NR	DH224NRK	HF224NR	H224NRB	200A HD DISC 2P FUSIBLE TYP3R 240V

Heavy Duty 240V-Fusible 3 Phase

MHF321N	DH321NGK	HF321N	H321N	30A HD DISC 3P FUSIBLE TYP1 240V
MHF321NR	DH321NRK	HF321NR	H321NRB	30A HD DISC 3P FUSIBLE TYP3R 240V
MHF322N	DH322NGK	HF322N	H322N	60A HD DISC 3P FUSIBLE TYP1 240V
MHF322NR	DH322NRK	HF322NR	H322NRB	60A HD DISC 3P FUSIBLE TYP3R 240V
MHF323N	DH323NGK	HF323N	H323N	100A HD DISC 3P FUSIBLE TYP1 240V
MHF323NR	DH323NRK	HF323NR	H323NRB	100A HD DISC 3P FUSIBLE TYP3R 240V
MHF324N	DH324NGK	HF324N	H324N	200A HD DISC 3P FUSIBLE TYP1 240V
MHF324NR	DH324NRK	HF324NR	H324NRB	200A HD DISC 3P FUSIBLE TYP3R 240V

Heavy Duty 600V-Fusible 3 Phase

MHF361	DH361FGK	HF361	H361N	30A HD DISC 3P FUSIBLE TYP1 600V
MHF361R	DH361FRK	HF361R	H361RB	30A HD DISC 3P FUSIBLE TYP3R 600V
MHF362	DH362FGK	HF362	H362N	60A HD DISC 3P FUSIBLE TYP1 600V
MHF362R	DH362FRK	HF362R	H362RB	60A HD DISC 3P FUSIBLE TYP3R 600V
MHF363	DH363FGK	HF363	H363N	100A HD DISC 3P FUSIBLE TYP1 600V
MHF363R	DH363FRK	HF363R	H363RB	100A HD DISC 3P FUSIBLE TYP3R 600V
MHF364	DH364FGK	HF364	H364N	200A HD DISC 3P FUSIBLE TYP1 600V
MHF364R	DH364FRK	HF364R	H364RB	200A HD DISC 3P FUSIBLE TYP3R 600V

Heavy Duty 240V-Non-Fusible 3 Phase (compact switch)

MHU321	--	HNF321N	H321N	30A HD DISC 3P NONFUSE TYP1 240V
---------------	----	---------	-------	----------------------------------

Heavy Duty 600V-Non-Fusible 3 Phase

MHU361	DH361UGK	HNF361	HU361	30A HD DISC 3P NONFUSE TYP1 600V
MHU361R	DH361URK	HNF361R	HU361RB	30A HD DISC 3P NONFUSE TYP3R 600V
MHU362	DH362UGK	HNF362	HU362	60A HD DISC 3P NONFUSE TYP1 600V
MHU362R	DH362URK	HNF362R	HU362RB	60A HD DISC 3P NONFUSE TYP3R 600V
MHU363	DH363UGK	HNF363	HU363	100A HD DISC 3P NONFUSE TYP1 600V
MHU363R	DH363URK	HNF363R	HU363RB	100A HD DISC 3P NONFUSE TYP3R 600V
MHU364	DH364UGK	HNF364	HU364	200A HD DISC 3P NONFUSE TYP1 600V
MHU364R	DH364URK	HNF364R	HU364RB	200A HD DISC 3P NONFUSE TYP3R 600V