




Front View



Right Side View



Knockout View




Knockouts

SYMBOL	SIZE	QTY.
A	9/32KO	4
B	1/2 KO	28
C	1/2 X 3/4 KO	15
D	1/2 X 3/4 X 1 KO	1
E	1/2 X 3/4 X 1 X 1 1/4 KO	6
F	1 X 1 1/4 X 1 1/2 X 2 KO	2
G	1 X 1 1/2 X 2 X 2 1/2 KO	5
H	1 X 1 1/4 X 1 1/2 X 2 X 2 1/2 KO	2
I	.219 X .08 OBLONG KO	4

Wire Range Size

(1) #6 - 250MCM (CU/AL)

Bottom View



Note : All Dimensions have ±0.125 Tolerance

NOTE: ALL KO LOCATING DIMENSIONS ARE INSIDE OF BOX.



Midwest Electric Products
Plainville, CT

MIDWEST LOAD CENTER 20/40 CIRCUIT 200A MLO N1
METALLIC ENCL SURFACE/FLUSH TOP/BOTTOM FEED

CAT NO	DWG DATE	REV #
MLM2020CCU	03/29/2017	01