


KNOCKOUT TABLE:

G= 1/2", 3/4", 1", 1-1/4", 1-1/2" KO
H= 1/2", 3/4", 1", 1-1/4", 1-1/2"-2" KO
I= 1/2", 3/4", 1" CONCENTRIC KO

WIRE RANGE TABLE:

CONNECTOR	COPPER		ALUMINIUM	
	SOLID	STRANDED	SOLID	STRANDED
LINE METER SOCKET	-	6-350	-	6-350
LOAD	14-10	14-10	-	-
NEUTRAL-"A"(LARGE HOLE)	14-4	12-4	12-4	12-4
NEUTRAL-"A"(SMALL HOLE)	14-8	12-8	12-8	12-8
NEUTRAL-"B"	-	1-300	-	1-300
EQUIP. GRND."C"	12-8	12-2	12-8	12-2

	CIRCUIT PROTECTION	NAME	QUANTITY
MAIN (1 & 2)	THQL21100	2P 120/240V 100AMP	1
K (3 & 4)	THQL1120	1 POLE 120/240V 20AMP	2



Part must conform to SI 900000 Sect. 4, Toxicity Procedure

FOR ADDITIONAL INFO REFER TO: APPLIED PRACTICES	SIGNATURES MODEL: TEJA CHINTALA DETAIL: TEJA CHINTALA	DATE 12/06/22 12/06/22	<p>Midwest Electric Products</p>
DIMENSIONS ARE IN INCHES	CHECKED: WILL	12/06/22	
UNLESS OTHERWISE SPECIFIED IN DRAWING	ENGRG:		<p>TITLE: R111MBC010U01.MD MIDWEST POWER 100A METERED RINGLESS (2) 20A GFCI 120/240V 1PH OUTLET METERED OUTLET METERED</p> <p>OUTLINE DRAWING</p> <p>TEMPORARY SERVICE EQUIPMENT</p>
TOLERANCE ON: 1 PL DECIMALS ± 0.1 2 PL DECIMALS ± 0.02 3 PL DECIMALS ± 0.005 ANGLES ± 1.0	MFG:		
FRACTIONS ± FINISH	QUALITY:		
CRITICAL TO QUALITY CHARACTERISTIC	ISSUED:		
	DRAWING FILE: R111MBC010U01.MD		SIZE: D
	SOLID MODEL: R111CB2010M01		DRAWING: R111MBC010U
			REV: D
			SHEET 1 OF 1