



Fig. A
R155MBC033U
MAY 2010

KNOCKOUT TABLE:

G= 1/2" - 3/4" - 1" KO
W= 1/2" - 3/4" - 1" - 1 1/4" - 1 1/2" - 2" KO
D= 3/4" - 1" - 1 1/4" KO

	CIRCUIT PROTECTION	NAME	QUANTITY
MAIN (1 & 2)	THHQL2170	2P 120/240V 70AMP	1
"E" (3 & 4)	THQL2150GFT2	GFCI 2P 120/240V 50AMP	1
"F" 5	THQL1120	1 POLE 120/240V 20AMP	1

WIRE RANGE TABLE:

CONNECTOR	COPPER		ALUMINIUM	
	SOLID	STRANDED	SOLID	STRANDED
LINE- METERSOCKET	-	6-350	-	6-350
LOAD-PLUG/DUPLEX	14-10	14-10	-	-
NEUTRAL (END HOLE)	12-8	12-1/0	10-8	10-1/0
NEUTRAL (SIDE HOLE)	14-8	14-4	12-10	12-4
EQUIP. GRND	12-8	12-2	12-8	12-2
NEUTRAL- "H"	--	1-300	--	1-300

Midwest Electric Products

TITLE
R155MBC033UM01 OUTLINE DRAWING/
9X30 70A 120/240 EZ 50/20 W/MAIN BKR
TEMPORARY POWER SERVICE EQUIPMENT

SIZE D	MODEL R155MBC033U	REV C
-----------	----------------------	----------

SCALE: 1:5 SHEET 1 OF 1