

Configuration






Fig. D
M281CB1, M281CB1GP, R281CB1,
R281CB1EP, R281CB1ETG, R281CB1GP
Series


Top View





Front View Interior




Front View Inside Cover



Front View External # 1




Side View



Circuit Protection

THQMV200WLBP



KNOCKOUT TABLE:

F= 1/2"
N= 1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
X= 1/2", 3/4", 1", 1-1/4", 1-1/2", 2", 2-1/2"
Y= 1-1/4", 1-1/2", 2", 2-1/2", 3"

Wire Range Size

WIRE RANGE TABLE

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRAND	SOLID	STRAND
LINE METER SOCKET	----	6-350	----	6-350
LOAD PHASE LINES	----	1-4/0	----	1-4/0
NEUTRAL A	----	6-350	----	6-350
NEUTRAL/GRND. B	----	6-2/0	----	6-2/0
NEUTRAL/GRND. C	14-8	14-4	12-8	12-4



MIDWEST SERVICE EQUIP 200A RINGLESS METERED SURFACE MT (ENERGY) UNDERGROUND FEED 120/240V 4 SPACES N3R UL LISTED

CAT NO	DWG DATE	REV #
R281CB1ETG	09/18/2024	02