


## GE ZENITH SERIES RDU-SC INPUT CONFIGURATIONS

- SYSTEM "A"**  
 SINGLE INPUT  
 Two panelboards 84 poles  
 450A Max. Input  
 24" DEEP SYSTEM  
 42" DEEP SYSTEM
- SYSTEM "B"**  
 DUAL INPUT  
 Two panelboards 84 poles  
 225A Max. Input per feed  
 24" DEEP SYSTEM  
 42" DEEP SYSTEM
- SYSTEM "C"**  
 DUAL INPUT  
 Four panelboards 168 poles  
 450A Max. Input per feed
- SYSTEM "D"**  
 FOUR INPUTS  
 Four panelboards 168 poles  
 225A Max. Input per feed
- SYSTEM "E"**  
 SINGLE INPUT  
 Four panelboards 168 poles  
 450A Max. Input



NOTES: 2.1 SYSTEM "A" AND "B" CONFIGURED IN A 24" DEEP AS STANDARD OR 42" DEEP AS OPTIONAL ENCLOSURE.  
 2.2 SYSTEM "C", "D" AND "E" CONFIGURED IN A 42" DEEP ENCLOSURE.

SIZE B	DWG. NO. 92-10500-00	REV A01
SCALE: NONE		PART NO.