

SK15-90TMB		
SKU	Description (as used in product)	Parts qty
4600134879P	Aux contact TME AUX-C 1Q 1SY 250V AC/DC T4/T6	1
4600134878P	Breaker TME Tmax T5N400 UL/CSA TMA 400-2000..4000 3p FF	1
8600089545P	CT TLE M output current	1
8600089537P	Display TLE M	1
4600089587P	Fan TLE M	1
4600089587P	Fan TLE M	1
1021099	FUSE 400A_660V_SZ.1_SEMIC_WITH IND.+USW	6
4600089588P	Fuse TLE M PS 5.2*20 8 A	1
8600089377P	PCB TLE M DR7 SSM driver	1
8600089376P	PCB TLE M DR9 Battery start	1
8600089379P	PCB TLE M EM4 In/Out/Bat EMI	1
8600089378P	PCB TLE M EM5 Main input EMI	1
8600089368P	PCB TLE M FR EMI DC input	1
8600089373P	PCB TLE M KY1 Panel buttons	1
8600089380P	PCB TLE M MN2 monitoring brd	1
8600089369P	PCB TLE M PW3 Power supply	1
8600089371P	PCB TLE M TF1 Power mod interface	1
8600089372P	PCB TLE M TF2 Monitor interf. 1	1
8600089374P	PCB TLE M TF3 dry contacts	1
8600089375P	PCB TLE M TF4 Monitor interf. 2	1
8600089381P	Sensor TLE M temperature	1
4600134880P	Shunt release TME YO-Cabled 220-240V AC/220-250V DC-T4/6	1
8600089709P	Switch TLE M Cold Start	1
4600089565P	Thyristor TLE M 273 A/1200V	3
27114	TME 15/30kVA Power Module UL/CE	1