



Top View




Knockouts

L= 1/2", 3/4" KO
G= 1/2", 3/4", 1" KO
M= 1/2", 3/4", 1", 1-1/4" KO


Left Side View




Back View




Front Cover



Right Side View



Bottom View



Wire Range Size

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRAND	SOLID	STRAND
LINE	14-8	14-2	12-8	12-2
LOAD	14-8	14-2	12-8	12-2
NEUTRAL	-----	-----	-----	-----
EQUIP. GRND.	12-8	12-2	12-8	12-2



Industrial Solutions

by ABB

60A GD AC DISCONNECT PULLER-TYPE 240V NON-FUSIBLE 10HP 15A GFI RECEPT STEEL N3R ENCL

CATNO

DWGDATE

REV#

TFN60RGFR

04/07/2020

03