

MAIN BREAKER MODULE

CATALOG NO. TMP3BU12R
TYPE 3R ENCLOSURE-RAINPROOF-1200 AMP MAX.
120/240V AC 1 PHASE-3 WIRE
208Y/240V AC 3 PHASE-4 WIRE
240/120V AC 3 PHASE-4 WIRE

For use with TMP or TMPR meter modules and TMP main lug module.

Suitable only for bottom feed.

SUITABLE FOR USE AS SERVICE EQUIPMENT.

USE COPPER OR ALUMINUM WIRE USE 75°C WIRE

TORQUE MAIN BUS JOINT BOLTS 300 LB.-INS.

REPLACEMENT PARTS/ACCESSORIES

End Cap - Right (Deep)	TMECR
End Cap - Left (Flat)	TMECL
Drip Hood	TMDH9
Hardware Kit	TMPMSK1

LUG SPECIFICATIONS

Function	Wire Size CU-AL AWG/MCM	Torque Lb.-In.
Grounding Terminal	(2) 4-300	250

SHORT CIRCUIT CURRENT RATING

This circuit breaker main is U.L. listed for use on a circuit delivering not more than 65,000 RMS SYM amperes at 240 VAC max. when a Eaton type NGS circuit breaker is installed. Replacement breaker shall be EATON of the same type and interrupting capacity. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module used.

The following U.L. Listed crimp connectors may be used.

Wire Size Cu only MCM	Manufacturer & Cat. No.			
	Mac	T & B	Bundy	Panduit
250	M8B250-8N MRB250-8N	54375 549688E	YA29-2LN YA29-3N	LCC250-12
300	M8B300-8N MRB300-8N	54380 549708E	YA30-2LN YA30-3N	LCC300-12
350	M8B350-8N MRB350-8N	54382 549728E	YA31-2LN YA31-3N	LCC350-12
400	M8B400-8N MRB400-8N	54874	YA32-2LN YA32-3N	LCC400-12
500	M8B500-8N MRB500-8N	54386 549788E	YA34-2LN YA34-3N	LCC500-12
600	M8B600-8N MRB600-8N	54388 549788E	YA36-2LN YA36-3N	-
700	-	54391	-	-
750	M8B750-8N MRB750-8N	54393 549808E	YA38-2LN YA38-3N	LCC750-12
Wire Size Cu-Al MCM				
250	MLB250-8N MULB250-8N	60258	YA29A3 YA29AY-2N	LAB250-12
300	MLB300-8N MULB300-8N	60262	YA30A3 YA30AY-2N	LAB300-12
350	MLB350-8N MULB350-8N	60267	YA31A3 YA31AY-2N	LAB350-12
400	MLB400-8N MULB400-8N	60269	YA32A3 YA32AY-2N	LAB400-12
500	MLB500-8N MULB500-8N	60273	YA34A3 YA34AY-2N	LAB500-12
600	MLB600-8N MULB600-8N	60275	YA36A3 YA36AY-2N	LAB600-12
700	-	60277	-	-
750	-	-	-	LCC750-12

Torque 12-13 crimp lug mounting nuts to 40-44 lb.-ft.

GENERAL ELECTRIC

E11713
PUB 52916

MADE IN U.S.A.

Rev. 1