

**MAIN BREAKER MODULE**

CATALOG NO. TMP3BU4R  
 TYPE 3R ENCLOSURE-RAINPROOF-400 AMP MAX.  
 120/240V AC 1 PHASE-3 WIRE  
 208Y/240V AC 3 PHASE-4 WIRE  
 240/120V AC 3 PHASE-4 WIRE

For use with TMP or TMPR meter modules and TMP main lug module.

Suitable only for bottom feed.

SUITABLE FOR USE AS SERVICE EQUIPMENT.

USE COPPER OR ALUMINUM WIRE USE 75°C WIRE

TORQUE MAIN BUS JOINT BOLTS 300 LB.-INS.

**REPLACEMENT PARTS/ACCESSORIES**

End Cap - Right (Deep)	TMECR
End Cap - Left (Flat)	TMECL
Drip Hood	TMDH9
Hardware Kit	TMPMSK1

**LUG SPECIFICATIONS**

Function	Wire Size CU-AL AWG/MCM	Torque Lb.-In.
Grounding Terminal	(2) 4-300	250

**SHORT CIRCUIT CURRENT RATING**

This circuit breaker main is U.L. listed for use on a circuit delivering not more than 65,000 RMS SYM amperes at 240 VAC max. when a Eaton type KD circuit breaker is installed. Replacement breaker shall be EATON of the same type and interrupting capacity. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module used.

The following U.L. Listed crimp connectors may be used.

Wire Size Cu only MCM	Manufacturer & Cat. No.			
	Mac	T & B	Burdry	Pendult
250	MSB250-8N	54775	YA29-3LN	LCC250-12
300	MRB250-8N	54888E	YA29-3N	LCC300-12
	MSB300-8N	54780	YA30-3LN	
350	MRB300-8N	54708E	YA30-3N	LCC350-12
	MSB350-8N	54282	YA31-3LN	
400	MRB350-8N	848728E	YA31-3N	LCC400-12
	MSB400-8N	54874	YA32-3LN	
500	MRB400-8N	54786	YA32-3N	LCC500-12
	MSB500-8N	548788E	YA34-3LN	
600	MRB500-8N	54289	YA34-3N	-
	MSB600-8N	548788E	YA35-3LN	
700	-	54291	YA35-3N	-
750	MSB750-8N	54223	YA39-3LN	LCC750-12
	MRB750-8N	548808E	YA39-3N	
Wire Size Cu-Al MCM				
250	MLB250-8N	60258	YA30A3	LAB250-12
300	MULB250-8N	60282	YA30AY-3N	LAB300-12
	MLB300-8N		YA30A3	
350	MULB300-8N	60287	YA30AY-2N	LAB350-12
	MLB350-8N		YA31A3	
400	MULB350-8N	60289	YA31AY-2N	LAB400-12
	MLB400-8N		YA32A3	
500	MULB400-8N	60273	YA32AY-2N	LAB500-12
	MLB500-8N		YA34A3	
600	MULB500-8N	60275	YA34AY-2N	LAB600-12
	MLB600-8N		YA36A3	
700	MULB600-8N	60277	YA36AY-2N	-
750	-	-	-	LCC750-12

Torque 1/2-13 crimp lug mounting nuts to 40-44 lb.-ft.

**GENERAL ELECTRIC**



E11713  
 PUB 52908

MADE IN U.S.A.

Rev. 1