




Top View




Front View (Outside)





Front View (Inside)



Side View - Left



Side View - Right



Bolted Pressure Switch type unit
Bottom of unit (incoming) has blank end walls

- NOTE:
1. FINISH - GRAY BAKED ENAMEL ON GALVANIZED STEEL.
 2. UL LISTED - FILE E44641.
 3. SUITABLE FOR USE AS SERVICE EQUIPMENT.
 5. NEUTRAL INSULATED, BONDABLE.
 6. 100% LOAD BREAK RATED.
 7. SHORT CIRCUIT CURRENT RATINGS:
100,000 RMS SYMMETRICAL AMPERES, 240 VAC WHEN USED WITH CLASS L FUSES.
 8. DUAL DIMENSIONS, INCHES [MILLIMETERS].

| TERMINAL LUGS INFORMATION | | | |
|----------------------------------|----------------|------------------|----------|
| LOCATION | MIN. WIRE SIZE | MAX. WIRE SIZE | TYPE |
| LINE, LOAD & NEUTRAL LUGS | | | |
| 4 PER POLE PROVIDED FOR 1200 AMP | (1) 1/0 AWG OR | (1) 750 kcmil OR | AL OR CU |
| 6 PER POLE PROVIDED FOR 1600 AMP | (2) 1/0 AWG | (2) 300 kcmil | |
| 8 PER POLE PROVIDED FOR 2000 AMP | | | |
| GROUND LUG (5 PROVIDED) | #6 AWG | 250 kcmil | AL OR CU |



imagination at work

METER MOD III-1200A MAIN FUSIBLE SWITCH N3R ENCL
100KAIC 3PH 4W 208Y/120V BOTTOM FEED W/ SHUNT TRIP

| REF NO | CAT NO | DWG DATE | REV # |
|---------|-------------|----------|-------|
| 96-7083 | TMP3FB12RST | 2/7/2017 | 01 |