

# MAIN SWITCH MODULE

CATALOG NO. TMP3FB4R  
 TYPE 3R ENCLOSURE - RAINPROOF - 400AMP  
 120/240VAC 1PH-3W  
 208Y/120VAC 3PH-4W  
 240/120VAC 3PH-4W

For use with TMP or TMPR meter modules and TMP main lug module. Continuous load current not to exceed 80% of the rating of fuses employed in other than motor circuits.

REPLACEMENT PARTS		TORQUE MAIN BUS JOINT BOLTS 300 LB-INS.
End Cap-Right (Deep)	TMECR	
End Cap-Left (Flat)	TMECL	
Switch Assembly (Complete)	TMP3FBS4	
Front Cover	TMFC1	
Drip Hood	TMDH9	
Handle	TMPFH1	
Hardware Kit	TMPMSK1	
Shroud	TMPSH1	
SUITABLE FOR USE AS SERVICE EQUIPMENT		
USE COPPER OR ALUMINUM WIRE USE 75°C WIRE.		

## LUG SPECIFICATIONS

FUNCTION	Wire Size CU-AL AWG/MCM	Torque lb.-ins.
Line Terminals	(1) 1/0-750 or (2) 1/0-300	550
Neutral Terminal	(1) 1/0-750 or (2) 1/0-300	550
Grounding Terminal	4-3000	250

## SHORT CIRCUIT INTERRUPTING RATING

This module is U.L. listed for use on circuits delivering not more than 100,00 RMS symmetrical amperes at 240 volts maximum when Class T fuses are installed. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TPM main lug module used.

