

# MAIN SWITCH MODULE

**CATALOG NO. TMP3FB6R**  
**TYPE 3R ENCLOSURE — RAINPROOF — 600 AMP**  
**120/240V AC 1 Ph-3W**  
**208Y/120V AC 3 Ph-4W**  
**240/120V AC 3 Ph-4W**

For use with TMP or TMPR meter modules and TMP main lug module. Continuous load current not to exceed 80% of the rating of fuses employed in other than motor circuits.

## REPLACEMENT PARTS

End Cap — Right (Deep)	TMECR
End Cap — Left (Flat)	TMECL
Switch Assembly (Complete)	TMP3FBS6
Front Cover	TMFC1
Drip Hood	TMDH9
Handle	TMPFH1
Hardware Kit	TMPMSK1
Shroud	TMPSH1

## TORQUE MAIN BUS JOINT BOLTS 300 LB-INS.

Suitable only for bottom feed.

SUITABLE FOR USE AS  
SERVICE EQUIPMENT

USE COPPER OR ALUMINUM WIRE  
USE 75°C WIRE

## LUG TORQUES

Function	Wire Size (CU-AL) AWG/MCM	Torque lb.-ins.
Line Terminals	(2) 2-600	500
Neutral Terminal	(2) 2-600	500
Grounding Terminal	4-300	250

## SHORT CIRCUIT INTERRUPTING RATING

This module is U.L. listed for use on circuits delivering not more than 100,000 RMS symmetrical amperes at 240 volts maximum when Class T fuses are installed. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module used.

**GENERAL  ELECTRIC**